

Eaton P2LM2CHJ4/UNV1

Catalog Number: P2LM2CHJ4/UNV1

Eaton Crouse-Hinds series Vaporgard Pro P2L LED, 0.12A, Cool white, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 1700 lm, Copper-free alum, Stanchion 25°, 1-1/4", 120-277 Vac, 14W



General specifications

| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Vaporgard Pro P2L LED light fixture | P2LM2CHJ4/UNV1 |
| | UPC |
| | 662276840157 |
| Product Length/Depth | Product Height |
| 11.69 in | 8.13 in |
| Product Width | Product Weight |
| 8.75 in | 6.5 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

1700

Color temperature

Cool white

Mounting Method

Stanchion 25° angled

Trade size

1-1/4"

Voltage rating

120-277 Vac

Drive type

AC

Frequency rating

50/60 Hz

Lens material

Heat and impact resistant glass

Wattage

14W

Amperage Rating

0.12 A

Material

Copper-free aluminum

Power factor

> 0.9

Guard

Without guard

Equivalent luminaire

50W HID or 150-200W incandescent

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED brochure](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

Catalogs

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED catalog page](#)

Certification reports

[Vaporgard Pro P2L Industrial LED Light Fixtures Canadian certification](#)

Installation instructions

[IF 1627 - Vaporgard Pro P2L LED](#)

[IF 1884 - Vaporgard Pro Driver Modules - AC Version](#)

Specifications and datasheets

[Eaton Specification Sheet - P2LM2CHJ4/UNV1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)