

# Specifications



## Eaton P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K

### General specifications

<b>PRODUCT NAME</b>	Eaton Mini-Power center
<b>CATALOG NUMBER</b>	P48G11S15P
<b>UPC</b>	786680140228
<b>PRODUCT LENGTH/DEPTH</b>	11.6 in
<b>PRODUCT HEIGHT</b>	37.5 in
<b>PRODUCT WIDTH</b>	13.1 in
<b>PRODUCT WEIGHT</b>	232 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	NEMA Compliant
<b>CERTIFICATIONS</b>	ANSI IEEE Certified UL Listed CSA Certified



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	286
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	107A15K

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	15 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
MULTIMEDIA	<a href="#">Eaton's Transformer Flex Center</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - P48G11S15P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K

### General specifications

<b>PRODUCT NAME</b>	Eaton Mini-Power center
<b>CATALOG NUMBER</b>	P48G11S15P
<b>UPC</b>	786680140228
<b>PRODUCT LENGTH/DEPTH</b>	11.6 in
<b>PRODUCT HEIGHT</b>	37.5 in
<b>PRODUCT WIDTH</b>	13.1 in
<b>PRODUCT WEIGHT</b>	232 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	NEMA Compliant
<b>CERTIFICATIONS</b>	ANSI IEEE Certified UL Listed CSA Certified



Powering Business Worldwide

## Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	286
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	107A15K

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	15 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
MULTIMEDIA	<a href="#">Eaton's Transformer Flex Center</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - P48G11S15P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

