



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P638RT Pan-Term® P6-38R-T Ring T *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | P638RT |
| Manufacturer | Panduit Corporation |
| Description | Ring Terminal, Large Wire, 6 Awg, 3/8" Stud Size, Non-Insulated, Bulk Package. |
| Weight per unit | 0.0102 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------|---------------|
| connection | Standard |
| insulation | Non-Insulated |
| Material | Copper |
| Voltage Rating | 2000 |
| Wire Size | #6 |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Tin-Plated |
|--------|------------|

Dimensions and Weight

| | |
|------|------|
| Size | 3/8" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | PAN-TERM® P6-38R-T RING T |
| extra long description | PAN P6-38R-T Pan-Term® P6-38R-T Rin |
| Long Description | Ring terminal, large wire, 6 AWG, 3/8" stud size, non-insulated, bulk package. |
| Product Type | Pan-Term® P6-38R-T Ring Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983870752 |
| Manufacturers Part Number | P6-38R-T |
| UPC | 074983870752 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Packaging

| | |
|-----------------|--------|
| Carton | 200 |
| Weight Per each | 0.0102 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Enclosure | Ring shape |
| Mounting | 7/16 |
| standard | cULus Listed 587H E52164, CSA Certified LR31212 |
| Temperature Rating | 302 Degrees Fahrenheit (150 Degrees Celsius) |