



SKU: PBT-350

UPC: 0783669077049

Features & Benefits:

Description: Nimbus Insulated Aluminum In-Line Splicer-Reducer Connector, Conductor Range 350-6, 2 Ports, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Contains DE-OX®	Yes
Number of Conductors	2
Number of Poles	1
Number of Ports / Wireways	2
Number of Usable Ports	2
Replacement Part(s)	PORTPLUG-350, SCREWCAP-350

Dimensions

Drive Size Main	5/16
Drive Type Main	Internal Hex
Height (IN)	2.432
Height BX (IN)	3.125
Height (mm)	61.7728
Length (IN)	4.046
Length (mm)	102.7684
Max Insulation OD (IN)	0.86
Max Insulation OD (mm)	21.844
Weight (LB)	0.51
Weight BX (LB)	1.153
Width (IN)	1.312
Width BX (IN)	3.875
Width (mm)	33.3248

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	Plastisol
Material	Aluminum
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	11/16
Wire Binding Torque	300 - 350 kcmil = 350

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 2
Dual Rated	Yes
NEMA Code	S-588-4
UPC Code	78366907704

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	350 kcmil - 6 Str
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	350 kcmil - 6 Str
Conductor Range CU Stranded (Secondary, tap, load)	NA
Conductor Range AL Solid (Primary, run, main, line)	NA
Flex Conductor Range	NA

Voltage

Voltage Rating	600 V
----------------	-------

Color

Cap Color Main	Black
Cap Color Tap	Black
Color	Black

Environment and Temperature

Environmental Conditions	Cold temperature rated to -45°C
Flammability Rating	Insulation rated per UL 94
Temperature Rating	90°C