

POOL & SPA Electromechanical Control

Swimming Pool Timers, 24 Hours P1100 Series



APPLICATIONS

1. **Real Time Switch Face:** Easy to set and check time.
2. **Captive Trippers:** 15 minute intervals, no lost trippers.
3. **Heater Contacts:** FM suffix includes "Fireman Switch" to turn off pool heater 20-30 minutes before timer turns OFF. Contact rates SPST, 15A @120V.
4. **Thermostat:** PFP models include built in Freeze Protection. No extra wiring. Thermostat turns on load at user settable level between 33°F and 42°F. Moving water prevents costly freeze damage.
5. **Accessory Contact:** PF models include extra contact to accept PFPT Freeze Protection Accessory. Thermostat turns ON load at user settable level between 33°F and 42°F. Moving water prevents costly freeze damage.
6. **Timer Interlock:** Makes one second timer dependant on operation of another timer.
7. **Quick Install/Release Lever:** For easy installation and removal when installing into pool panels.
8. **Load Indicator Lamp**
9. **Convenient External Rocker Switch:** 3 position switch: OFF/ON/AUTO. Use switch to turn OFF pump at the end of pool season.



| CAT. NO. | UPC CODE | INPUT SUPPLY (VAC) 60Hz | CONTACTS | RESISTIVE/INDUCTIVE RATINGS | HP RATING | NOTES |
|------------|----------|-------------------------|----------|-----------------------------|-----------------------------|--|
| PFP3-M | 94027 | 120/240 w/neutral | DPST | 40A | 3 HP @ 120V 7.5HP @ 240V | Thermostat only |
| P1101-M | 10056 | 120 | DPST | 40A | 3 HP @ 120V | — |
| P1101FM-M | 10060 | 120 | DPST | 40A | 3 HP @ 120V | Fireman Switch |
| PF1101-M | 94020 | 120 | DPST | 40A | 3 HP @ 120V | Accepts PFPT thermostat input |
| PF1101FM-M | 94024 | 120 | DPST | 40A | 3 HP @ 120V | Fireman Switch & Accepts PFPT thermostat input |
| PFP1103-M | 94023 | 120/240 w/neutral | DPST | 40A | 3 HP @ 120V 7.5HP @ 240V | Freeze Protection included |
| P1104-M | 10057 | 240 | DPST | 40A | 7.5HP @ 240V | — |
| P1104FM-M | 10061 | 240 | DPST | 40A | 7.5HP @ 240V | Fireman Switch |
| PF1104-M | 94021 | 240 | DPST | 40A | 7.5HP @ 240V | Accepts PFPT thermostat input |
| PF1104FM-M | 94025 | 240 | DPST | 40A | 7.5HP @ 240V | Fireman Switch & Accepts PFPT thermostat input |
| PFPT | 94028 | 120/240 | — | — | — | Thermostat accessory |

NOTE: " " = Indicates Freeze Protection.