



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## P1GY Wallplate, 1-G, Tog, Gy

*Hubbell Wiring Devices*

Catalog Number	P1GY
Manufacturer	Hubbell Wiring Devices
Description	Wallplate, Toggle, 1-Gang, Gray
Weight per unit	0.0500 (lbs/each)
Product Category	Wiring Devices

### Features

cutout	Toggle
Material	Polycarbonate thermoplastic
orientation	Vertical
pallet quantity	15400

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	4.63 in x 2.88 in x 0.25 in
------	-----------------------------

### Descriptions

Description	WALLPLATE, 1-G, TOG, GY
extra long description	HWDK P1GY WALLPLATE, 1-G, TOG, GY
Features	Hubbell's line of polycarbonate wallplates features larger standard sized wallplates to provide extra coverage to hide rough box opening, improved aesthetics, greater strength, impact resistance, along with easy to clean finish in all different types of environments. Hubbell's standard sized wallplates are 1/8 inch larger to provide you that extra coverage to hide rough box openings. The depth is 1/4 inch so that it will comfortably fit over the device even on imperfect installations or on retrofit work.
Long Description	Wallplate, Toggle, 1-Gang, Gray
Product Type	Wallplate, 1-G, Tog, Gy
Special Features	Smooth Satin Finish

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778311505
Manufacturers Part Number	P1GY
UPC	883778311505

### Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	TOGGLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 25

Weight Per each ..... 0.05

## Uses, Certifications, and Standards

Application ..... For use with Toggle Switch

Mounting ..... Painted Steel;Screw Mounting