

# 4" Dia. Round Outlet:

## Residential Units



### Series PC234-BH



For 16"-24" on center Joist applications

Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-BH*	16"-24" adj. bar hanger, molded-in Speed Klamps™	2-3/8	4	50 lb.	98032	24	28
23.0	PC234-BHG	16"-24" adj. bar hanger, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98033	24	28

### Series PC234-N



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-N	Angled Fetter ring nails, molded-in Speed Klamps™	2-3/8	4	50 lb.	98025	50	12
23.0	PC234-NG*	Angled Fetter ring nails, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98026	50	13

### Series PC234-16



For max 16" on center Joist applications only

Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
23.0	PC234-16	16" bar hanger, molded-in Speed Klamps™	2-3/8	4	50 lb.	98306	24	18
23.0	PC234-16G*	16" bar hanger, ground strap, molded-in Speed Klamps™	2-3/8	4	50 lb.	98307	24	18



\* Indicates model shown • See page 7 for Attachment Coding descriptions

