

# The Ultimate Ice Breaker



E.



F.



G.

**Rating:**

**PF1122T, PF1202T**

**Power Center Rating:** 92 A per leg, 168 A max.  
120/ 240 VAC or 120/240 VAC single phase, 60 Hz.  
**Power Center Dimensions:** 12" (30.5 cm) H x  
12" (30.5 cm) W x 4 1/4" (10.8 cm) D

**PF1222TB1**

**Load Center Rating:** 85 A max., 120, 240 VAC or  
120, 208 VAC single phase, 60 Hz.  
**Load Center Dimensions:** 20 3/4" (52.7 cm) H x  
12 3/4" (32.4 cm) W x 4 1/4" (10.8 cm) D

**Thermostat Range:** 33°F to 42°F (0.5°C to 5.5°C)  
with 5°F differential

**Switch Rating:**

- 30 A Resistive/Inductive, Tungsten or  
1000 VA Pilot Duty each pole 120, 208, 240 VAC
- 2 HP (24 FLA), 120 VAC
- 5 HP (28 FLA), 240 VAC

**Warranty:** 1 year

## PF1100 and PF1200 Series Control System with Freeze Protection and Power or Load Center



- For pools/spas requiring one or two time switches
- Protects pool/spa equipment against freeze damage
- GFCI and switch mounting capabilities
- Turns pump and heater ON when outdoor temperature drops below user-adjustable setpoint on thermostat
- Heavy-duty Type 3R steel Indoor/Outdoor power and load centers

Model #	Description	Input Voltage	HP	Heater Protection
E. PF1122T	Power Center with (1) Time Switch	240 VAC	3	No
F. PF1202T	Power Center with (2) Time Switches	240 VAC	3	No
G. PF1222TB1*	Load Center with (2) Time Switches	240 VAC	3	Yes

\*4/8 Breaker base and heater protection

For replacement parts, trippers and accessories see page 153

Wiring devices may be installed in this power or load center  
(order (4) 21T156A standoffs for mounting). See page 154.

# The Ultimate Ice Breaker



E.



F.



G.

**Rating:**

**PF112T, PF1202T**

**Power Center Rating:** 92 A per leg, 168 A max.  
120/ 240 VAC or 120/240 VAC single phase, 60 Hz.  
**Power Center Dimensions:** 12" (30.5 cm) H x  
12" (30.5 cm) W x 4 1/4" (10.8 cm) D

**PF1222TB1**

**Load Center Rating:** 85 A max., 120, 240 VAC or  
120, 208 VAC single phase, 60 Hz.  
**Load Center Dimensions:** 20 3/4" (52.7 cm) H x  
12 3/4" (32.4 cm) W x 4 1/4" (10.8 cm) D

**Thermostat Range:** 33°F to 42°F (0.5°C to 5.5°C)  
with 5°F differential

**Switch Rating:**

- 30 A Resistive/Inductive, Tungsten or 1000 VA Pilot Duty each pole 120, 208, 240 VAC
- 2 HP (24 FLA), 120 VAC
- 5 HP (28 FLA), 240 VAC

**Warranty:** 1 year

## PF1100 and PF1200 Series Control System with Freeze Protection and Power or Load Center



- For pools/spas requiring one or two time switches
- Protects pool/spa equipment against freeze damage
- GFCI and switch mounting capabilities
- Turns pump and heater ON when outdoor temperature drops below user-adjustable setpoint on thermostat
- Heavy-duty Type 3R steel Indoor/Outdoor power and load centers

Model #	Description	Input Voltage	HP	Heater Protection
E. PF112T	Power Center with (1) Time Switch	240 VAC	3	No
F. PF1202T	Power Center with (2) Time Switches	240 VAC	3	No
G. PF1222TB1*	Load Center with (2) Time Switches	240 VAC	3	Yes

\*4/8 Breaker base and heater protection

For replacement parts, trippers and accessories see page 153

Wiring devices may be installed in this power or load center (order (4) 21T156A standoffs for mounting). See page 154.