

# Specifications

Photo is representative



## Eaton PDG23G0070TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 70A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

### General specifications

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG23G0070TFFL
<b>UPC</b>	786679911723
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	104.6 mm
<b>PRODUCT WEIGHT</b>	1.82 kg
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA UL 489 CCC Marked IEC 60947-2

### Delivery program

<b>AMPERAGE RATING</b>	70A
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>FRAME</b>	2
<b>NUMBER OF POLES</b>	Three-pole

### Technical data - Electrical

<b>VOLTAGE RATING</b>	600 Vac
-----------------------	---------

### General information

<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CLASS</b>	Class A
<b>TRIP TYPE</b>	T298

### Technical data - Mechanical - Terminals

<b>TERMINALS</b>	Standard Terminals Load Only
------------------	------------------------------

## Technical information

**INTERRUPT RATING** 35 kAIC at 480 Vac

25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)

8 kAIC Icu/ 4 kAIC Ics/ 16.8

kAIC Icm @690V (IEC)

10 kAIC Icu @250 Vdc

35 kAIC @480V (UL)

20 kAIC Icu/ 15/13 kAIC Ics/

42 kAIC Icm @525V South

Africa (IEC)

10 kAIC Icu @ 125 Vdc

55 kAIC Icu/ 55 kAIC Ics/ 121

kAIC Icm @240V (IEC)

18 kAIC @600V (UL/CSA)

65 kAIC @240V (UL)

36 kAIC Icu/ 36 kAIC Ics/ 75.6

kAIC Icm @380-415V (IEC)

## INTERRUPT RATING RANGE

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Power Defense PDG23G0070TFFL 3D drawing](#)

### APPLICATION NOTES

[Consulting application guide - molded case circuit breakers](#)

[Power Defense technical selling booklet](#)

[Power Defense molded case circuit breaker selection poster](#)

### BROCHURES

[Power Defense brochure](#)

[Power Defense molded case circuit breakers - Frame 2 product aid](#)

### CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

[PDG2 CB report](#)

[PDG4 CB report](#)

### CERTIFICATION REPORTS

[Power Defense Declaration concerning California's Proposition 65](#)

[EU Declaration of Conformity - Power Defense molded case circuit breakers](#)

[PDG4 CCC certification](#)

### INSTALLATION INSTRUCTIONS

[Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN](#)

[Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions-IL012239EN H01](#)

[Power Defense Frame 2 tunnel terminal \(aluminum\), 150A, 3 pole instructions - IL012238EN H03](#)

[Power Defense Frame 2 multi wire connector kit - PDG2X3\(2\)\(4\)TA2256W instructions - IL012242EN H01](#)

[Power Defense Frame 2 box terminal \(aluminum\), 225A, 3 pole instructions - IL012235EN H03](#)

[Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN](#)

[Power Defense Frame 2 PDG2 and PDC\(E\)9 breaker instructions - IL012106EN](#)

[Power Defense Frame 1-2-3-4  
IP door barrier assembly  
instructions - IL012278EN](#)

[Power Defense Frame 2 Direct  
Rotary Handle Assy With  
Interlock Version Instructions  
\(IL012138EN\).pdf](#)

[Power Defense Frame 2 multi  
wire connector kit -  
PDG2X3\(2\)\(4\)TA2253W  
instructions - IL012243EN H01](#)

[Power Defense Frame 2 box  
terminal \(steel\), 100A, 3 pole  
instructions - IL012234EN H03](#)

[Power Defense Frame 2 handle  
mech direct rotary handle  
instructions - IL012134EN](#)

[Power Defense Frame 2 tunnel  
terminal \(aluminum\), 50A, 3  
pole instructions - IL012236EN  
H03](#)

[Power Defense Frame 2  
terminal kit -  
PDG2X3\(2\)\(4\)TA225RF  
instructions - IL012245EN H01](#)

[Power Defense Frame 2 screw  
terminal end cap kit, 225A, 3  
pole instructions - IL012258EN  
H01](#)

[Power Defense Frame 2  
locking devices and handle  
block instructions -  
IL012149EN](#)

[Power Defense Frame 2 clamp  
terminal \(steel\), 20A, 3 pole  
instructions - IL012246EN H03](#)

[Power Defense Frame 2  
terminal kit -  
PDG2X3\(2\)\(4\)TA150RF  
instructions - IL012244EN H01](#)

[Power Defense Frame 1 IEC  
and Frame 2 Rotary  
Mechanism with NFPA Handle  
Attachment Instructions  
\(IL012260EN\).pdf](#)

[Power Defense Frame 2 tunnel  
terminal \(aluminum\), 100A, 3  
pole instructions - IL012237EN  
H03](#)

[Power Defense Frame 2/3/4/5/6  
voltage neutral sensor module  
wiring instructions –  
IL012316EN](#)

[Power Defense Frame 2 shunt  
trip UVR instructions -  
IL012130EN](#)

	<a href="#">Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh</a>
	<a href="#">Power Defense Frame 2 withTMTU, Shunt Trip UVR Animated Instructions.rh</a>
<b>INSTALLATION VIDEOS</b>	<a href="#">Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh</a>
	<a href="#">Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh</a>
	<a href="#">Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh</a>
<b>MULTIMEDIA</b>	<a href="#">Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video</a>
	<a href="#">Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video</a>
	<a href="#">Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video</a>
	<a href="#">Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video</a>
	<a href="#">Power Defense molded case circuit breakers</a>
	<a href="#">Eaton Power Defense for superior arc flash safety</a>
	<a href="#">Power Defense Frame 5 Trip Unit How-To Video</a>
	<a href="#">Power Defense Frame 6 Trip Unit How-To Video</a>
	<a href="#">Power Defense Breakers</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - PDG23G0070TFFL</a>
<b>TIME/CURRENT CURVES</b>	<a href="#">Power Defense time current curve Frame 2 - PD2</a>
	<a href="#">Single and double break MCCB performance revisited</a>
	<a href="#">Molded case and low-voltage power circuit breaker health</a>
<b>WHITE PAPERS</b>	<a href="#">Making a better machine</a>
	<a href="#">Intelligent circuit protection yields space savings</a>
	<a href="#">Molded case and low-voltage breaker health</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative



## Eaton PDG23G0070TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 70A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

### General specifications

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG23G0070TFFL
<b>UPC</b>	786679911723
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	104.6 mm
<b>PRODUCT WEIGHT</b>	1.82 kg
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA UL 489 CCC Marked IEC 60947-2

### Delivery program

<b>AMPERAGE RATING</b>	70A
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>FRAME</b>	2
<b>NUMBER OF POLES</b>	Three-pole

### Technical data - Electrical

<b>VOLTAGE RATING</b>	600 Vac
-----------------------	---------

### General information

<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CLASS</b>	Class A
<b>TRIP TYPE</b>	T298

### Technical data - Mechanical - Terminals

<b>TERMINALS</b>	Standard Terminals Load Only
------------------	------------------------------

## Technical information

<b>INTERRUPT RATING</b>	35 kAIC at 480 Vac
<b>INTERRUPT RATING RANGE</b>	25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC) 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC) 8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC) 10 kAIC Icu @250 Vdc 35 kAIC @480V (UL) 20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu @125 Vdc 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC) 18 kAIC @600V (UL/CSA) 65 kAIC @240V (UL) 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)

## Resources

<b>3D CAD DRAWING PACKAGE</b>	<a href="#">Eaton Power Defense PDG23G0070TFFL 3D drawing</a>
<b>APPLICATION NOTES</b>	<a href="#">Consulting application guide - molded case circuit breakers</a> <a href="#">Power Defense technical selling booklet</a> <a href="#">Power Defense molded case circuit breaker selection poster</a> <a href="#">Power Defense brochure</a> <a href="#">Power Defense molded case circuit breakers - Frame 2 product aid</a>
<b>BROCHURES</b>	<a href="#">Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2</a>
<b>CATALOGS</b>	<a href="#">PDG2 CB report</a> <a href="#">PDG4 CB report</a> <a href="#">Power Defense Declaration concerning California's Proposition 65</a> <a href="#">EU Declaration of Conformity - Power Defense molded case circuit breakers</a> <a href="#">PDG4 CCC certification</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN</a> <a href="#">Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions-IL012239EN H01</a> <a href="#">Power Defense Frame 2 tunnel terminal (aluminum), 150A, 3 pole instructions - IL012238EN H03</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01</a> <a href="#">Power Defense Frame 2 box terminal (aluminum), 225A, 3 pole instructions - IL012235EN H03</a> <a href="#">Power Defense Frame 2 handle mech variable depth rotary handle instructions - IL012136EN</a> <a href="#">Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN</a>

[Power Defense Frame 1-2-3-4  
IP door barrier assembly  
instructions - IL012278EN](#)

[Power Defense Frame 2 Direct  
Rotary Handle Assy With  
Interlock Version Instructions  
\(IL012138EN\).pdf](#)

[Power Defense Frame 2 multi  
wire connector kit -  
PDG2X3\(2\)\(4\)TA2253W  
instructions - IL012243EN H01](#)

[Power Defense Frame 2 box  
terminal \(steel\), 100A, 3 pole  
instructions - IL012234EN H03](#)

[Power Defense Frame 2 handle  
mech direct rotary handle  
instructions - IL012134EN](#)

[Power Defense Frame 2 tunnel  
terminal \(aluminum\), 50A, 3  
pole instructions - IL012236EN  
H03](#)

[Power Defense Frame 2  
terminal kit -  
PDG2X3\(2\)\(4\)TA225RF  
instructions - IL012245EN H01](#)

[Power Defense Frame 2 screw  
terminal end cap kit, 225A, 3  
pole instructions - IL012258EN  
H01](#)

[Power Defense Frame 2  
locking devices and handle  
block instructions -  
IL012149EN](#)

[Power Defense Frame 2 clamp  
terminal \(steel\), 20A, 3 pole  
instructions - IL012246EN H03](#)

[Power Defense Frame 2  
terminal kit -  
PDG2X3\(2\)\(4\)TA150RF  
instructions - IL012244EN H01](#)

[Power Defense Frame 1 IEC  
and Frame 2 Rotary  
Mechanism with NFPA Handle  
Attachment Instructions  
\(IL012260EN\).pdf](#)

[Power Defense Frame 2 tunnel  
terminal \(aluminum\), 100A, 3  
pole instructions - IL012237EN  
H03](#)

[Power Defense Frame 2/3/4/5/6  
voltage neutral sensor module  
wiring instructions –  
IL012316EN](#)

[Power Defense Frame 2 shunt  
trip UVR instructions -  
IL012130EN](#)



	<a href="#">Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh</a>  <a href="#">Power Defense Frame 2 withTMTU, Shunt Trip UVR Animated Instructions.rh</a>  <a href="#">Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh</a>  <a href="#">Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh</a>  <a href="#">Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh</a>
<b>INSTALLATION VIDEOS</b>	<a href="#">Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video</a>  <a href="#">Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video</a>  <a href="#">Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video</a>  <a href="#">Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video</a>  <a href="#">Power Defense molded case circuit breakers</a>  <a href="#">Eaton Power Defense for superior arc flash safety</a>  <a href="#">Power Defense Frame 5 Trip Unit How-To Video</a>  <a href="#">Power Defense Frame 6 Trip Unit How-To Video</a>  <a href="#">Power Defense Breakers</a>
<b>MULTIMEDIA</b>	
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - PDG23G0070TFFL</a>
<b>TIME/CURRENT CURVES</b>	<a href="#">Power Defense time current curve Frame 2 - PD2</a>  <a href="#">Single and double break MCCB performance revisited</a>  <a href="#">Molded case and low-voltage power circuit breaker health</a>
<b>WHITE PAPERS</b>	<a href="#">Making a better machine</a>  <a href="#">Intelligent circuit protection yields space savings</a>  <a href="#">Molded case and low-voltage breaker health</a>

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

