



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## PH100PG 100 Va Mte CTRL XFRMR 120X240V-12X24V *Hammond Power Solutions*

Catalog Number	PH100PG
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 100va
Weight per unit	4.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

### Features

Wattage	100
---------	-----

### Dimensions and Weight

Height	3.63
Length	4.19
Width	3.25

### Descriptions

Description	100 VA MTE CTRL XFRMR 120X240V-12X24V
extra long description	HMND PH100PG CNTL 100VA 120x240-12x
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 100VA
Product Type	CNTL 100VA 120X240-12X24
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

### Manufacturer Information

Brand	HPS Imperator™
GTIN	00803423078140
Manufacturers Part Number	PH100PG
UPC	803423078140

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

### Packaging

Carton	1
Weight Per each	4.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum