



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PH150MQMJFK 150 Va Mte CTRL XFRMR 240X480V-120X240V W/Fusing *Hammond Power Solutions*

Catalog Number	PH150MQMJFK
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 150 Kva, Primary and Secondary Fuse Clips Included
Weight per unit	5.7 (lbs/each)
Product Category	Encapsulated Industrial Contro

### Features

Wattage	150
---------	-----

### Descriptions

Description	150 VA MTE CTRL XFRMR 240X480V-120X240V W/FUSING
extra long description	HMND PH150MQMJ-FK CNTL 150VA 240X48
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 150 kVA, Primary And Secondary Fuse Clips Included
Product Type	CNTL 150VA 240X480-120x240fuse
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

### Manufacturer Information

Brand	HPS Imperator®
GTIN	00803423081829
Manufacturers Part Number	PH150MQMJ-FK
UPC	803423081829

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

### Packaging

Carton	1
Weight Per each	5.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum