



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH750MQMJ 1PH 750VA 240X480V-120X240V 50/60HZ Cu *Hammond Power Solutions*

Catalog Number	PH750MQMJ
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 750 Kva
Weight per unit	16.6 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

Wattage	750
---------	-----

Dimensions and Weight

Height	4.31
Length	5.13
Width	6.69

Descriptions

Description	1PH 750VA 240X480V-120X240V 50/60HZ CU
extra long description	HMND PH750MQMJ CNTL 750VA 240X480-1
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 750 kVA
Product Type	CNTL 750VA 240X480-120X240
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS Imperator®
GTIN	00803423078003
Manufacturers Part Number	PH750MQMJ
UPC	803423078003

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Packaging

Carton	1
Weight Per each	16.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum