

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3101 Industrial Terrace 78758-0000, TX Austin Phone: 512-351-3290 Fax: 512-973-9027



Weight Per each

## PH75PG 1PH 75VA 120X240V-12X24V 50/60HZ Cu

Hammond Power Solutions

Catalog Number	PH75PG
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 75 Kva
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro
Features	
Wattage	75
Dimensions and Weight	
Height	3.56
Length	3.25
Width	3.88
Descriptions	
Description	1PH 75VA 120X240V-12X24V 50/60HZ CU
extra long description	HMND PH75PG CNTL 75 VA120/240SEC
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 75 kVA
Product Type	CNTL 75 VA120/240SEC 12X24
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.
Manufacturer Information	
Brand	HPS Imperator®
GTIN	00803423078133
Manufacturers Part Number	PH75PG
UPC	803423078133
Taxonomies, Classifications, and G	Categories
Category Description	CONTROL TRANSCORMERS
Туре	Tranformer > Dry Type > Control > Molded
Packaging	
Carton	1

3.54

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3101 Industrial Terrace 78758-0000, TX Austin Phone: 512-351-3290 Fax: 512-973-9027

## Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control
	Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum