




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN10L08FW PN10 8' Latching Raceway FW *Wiremold/Legrand*

Catalog Number	PN10L08FW
Manufacturer	Wiremold/Legrand
Description	<P>PN10 Series One-Piece Latching Raceway With CO-Extruded Hinge and Adhesive Bakcing. Available In 8' (2.44M) Lengths.</P>
Weight per unit	0.2120 (lbs/each)
Product Category	Non-Metallic Raceway & Accy.

Features

indoor/outdoor	Indoor
Material	Plastic
Number of Channels	1.0
Voltage	600.0 V

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	PN10 8' LATCHING RACEWAY FW
extra long description	WM PN10L08FW PN10 8FT LATCHING RCWY
Features	<p>PN10 Series One-piece latching raceway with co-extruded hinge and adhesive bakcing. Available in 8' (2.44m) lengths.</p>
Long Description	<p>PN10 Series One-piece latching raceway with co-extruded hinge and adhesive bakcing. Available in 8' (2.44m) lengths.</p>
Product Type	PN10 8FT Latching RcwY FW
Special Features	Designed for use with Ortronics® TracJack and Series II modules. PSB3 Device Box accommodates wireless. Accommodates communication or power wiring. FT-4 Flame Spread Rating.

Manufacturer Information

Brand	WIREMOLD
GTIN	00786776035438
Manufacturers Part Number	PN10L08FW
UPC	786776035438

Taxonomies, Classifications, and Categories

Category Description	Wire/Plug Strips, Surf Raceways, Power Pole, Walkerduct, & Plugmolds
Type	Raceway

Availability

minimum qty	8
-------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 160

Weight Per foot 0.212

Uses, Certifications, and Standards

standard ROHS, CULUS, cULus Listed Raceway: File E90378 Guide RJTX.
Complies with flammability requirements of UL-5A. Fittings: File
E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to
600V. Meets Section 12-2600 of CEC.