



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS15AC1L 15A 120/277VAC B+S Wire SP Lock SW Gy

Pass & Seymour/Legrand

Catalog Number	PS15AC1L
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Lock Switch, Back and Side-Wire, 15A 120/277V (Key Can Be Removed In Both Positions)
Weight per unit	0.2024 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Toggle
amperage rating	15
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	15 A @ 120/277 VAC
Load Type	Halogen, CFL, Incandescent, Xenon, Universal, Fluorescent, LED
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Locking, Toggle
throw type	Single Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	15A 120/277VAC B+S WIRE SP LOCK SW GY
extra long description	P&S PS15AC1L 15A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	1-Pole Lock Switch, Back and Side-Wire, 15A 120/277V (Key can be removed in both positions)
Product Type	15A 120/277VAC B+S Wire SP Lock SW Gry
Special Features	Heavy duty switch, back & side wire, shallow design for ease of installation



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195590
Manufacturers Part Number	PS15AC1-L
UPC	785007195590

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2024

Uses, Certifications, and Standards

Application	Commercial/Residential
Mounting standard	WALL CULUS, UL20, FEDSPEC