



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1010LFL Pan-Term® PN10-10LF-L Loo *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | PN1010LFL |
| Manufacturer | Panduit Corporation |
| Description | Locking Fork Terminal, Nylon Insulated, 12 - 10 Awg, #10 Stud Size, Standard Package. |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | Nylon |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Yellow |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|-----|
| Size | #10 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | PAN-TERM® PN10-10LF-L LOO |
| extra long description | PAN PN10-10LF-L Pan-Term® PN10-10LF |
| Long Description | Locking Fork Terminal, nylon insulated, 12 - 10 AWG, #10 stud size, standard package. |
| Product Type | Pan-Term® PN10-10LF-L Loose Piece Forks |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983800841 |
| Manufacturers Part Number | PN10-10LF-L |
| UPC | 074983800841 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | TERMINALS |
| Type | Locking Fork Terminal |

Packaging

| | |
|-----------------|-------|
| Carton | 50 |
| Package | 500 |
| Weight Per each | 0.275 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure | Fork shape |
| Mounting | 9/32 |
| standard | UL Listed 587H E52164; CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |