



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777



PN1014RD 12-10AWG 1/4"STD Nylon Insltd Ring TRML

Panduit Corporation

Catalog Number	PN1014RD
Manufacturer	Panduit Corporation
Description	The PN10-14R-D Pan-Term® Terminal Is A Nylon Insulated, Ring Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0061 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	1/4"
------	------

Descriptions

Description	12-10AWG 1/4"STD NYLON INSLTD RING TRML
extra long description	PAN PN10-14R-D Pan-Term® PN10-14R-D
Long Description	The PN10-14R-D Pan-Term® Terminal is a nylon insulated, ring terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN10-14R-D Ring Terminal, Yellow, Nylon, 10-12 Awg

Manufacturer Information

Brand	Panduit®
GTIN	00074983800353
Manufacturers Part Number	PN10-14R-D
UPC	074983800353



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Availability

minimum qty 500

Packaging

Carton 500

Weight Per each 0.0061

Uses, Certifications, and Standards

Enclosure Ring shape

Mounting 9/32

standard cULus Listed 587H E52164, CSA Certified LR31212, Military QPL
AS7928 (MS25036-157)

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)