



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587



PN1410RM 14-18AWG #10STD Nylon Insld Ring TRML

Panduit Corporation

Catalog Number	PN1410RM
Manufacturer	Panduit Corporation
Description	The PN14-10R-M Pan-Term® Terminal Is A Nylon Insulated, Ring Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0023 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	14-18AWG #10STD NYLON INSLTD RING TRML
extra long description	PAN PN14-10R-M Pan-Term® PN14-10R-M
Long Description	The PN14-10R-M Pan-Term® Terminal is a nylon insulated, ring terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN14-10R-M Ring Terminal, Blue, Nylon, 14-18 Awg,

Manufacturer Information

Brand	Panduit®
GTIN	00074983800216
Manufacturers Part Number	PN14-10R-M
UPC	074983800216



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6 South Hickory
71373-0000, LA Vidalia
Phone: 318-336-5113
Fax: 318-336-5587

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Availability

minimum qty 1000

Packaging

Carton 1000

Weight Per each 0.0023

Uses, Certifications, and Standards

Enclosure Ring shape

Mounting 7/32

standard cULus Listed 587H E52164, CSA Certified LR31212, Military QPL
AS7928 (MS25036-108)

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)