




Pass & Seymour

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip® M³ 15 & 20A, 125 & 250V

PS5965-Y, PS5965-GRY, PS5965-O, PS5969-Y, PS5969-GRY, PS5969-O,
PS5364-Y, PS5364-GRY, PS5369-Y, PS5369-GRY, PS5666-Y, PS5669-Y,
PS5464-Y, PS5469-Y

Easy assembly and a durable design.

With their tri-drive assembly and terminal screws in addition to self-hinged nylon housings, MaxGrip M³ plugs and connectors install quickly and easily. They stay installed, too — because their rugged construction and high-retention cord grips help them shrug off impacts and constant use.



Features & Benefits

High-visibility yellow and orange, or gray.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

Self-hinge swings wide open to make quick, easy work of tight, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.

PS5965-Y and PS5969-Y

Tough nylon construction with crush/impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.

Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

SF502R2 – Updated March 2008 – For latest specs visit www.legrand.us/passandseymour

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip[®] M³ 15 & 20A, 125 & 250V

Ordering Information

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.
MaxGrip[®] M³ Plugs & Connectors				
PS5965-Y	15 125	Plug, Yellow	.230"-.720"	5-15P
PS5965-GRY	15 125	Plug, Gray	.230"-.720"	5-15P
PS5965-O	15 125	Plug, Orange	.230"-.720"	5-15P
PS5969-Y	15 125	Connector, Yellow	.230"-.720"	5-15R
PS5969-GRY	15 125	Connector, Gray	.230"-.720"	5-15R
PS5969-O	15 125	Connector, Orange	.230"-.720"	5-15R
PS5364-Y	20 125	Plug, Yellow	.230"-.720"	5-20P
PS5364-GRY	20 125	Plug, Gray	.230"-.720"	5-20P
PS5369-Y	20 125	Connector, Yellow	.230"-.720"	5-20R
PS5369-GRY	20 125	Connector, Gray	.230"-.720"	5-20R
PS5666-Y	15 250	Plug, Yellow	.230"-.720"	6-15P
PS5669-Y	15 250	Connector, Yellow	.230"-.720"	6-15R
PS5464-Y	20 250	Plug, Yellow	.230"-.720"	6-20P
PS5469-Y	20 250	Connector, Yellow	.230"-.720"	6-20R



NEMA
5-15R



NEMA
5-15P



NEMA
6-15R



NEMA
6-15P



NEMA
5-20R



NEMA
5-20P



NEMA
6-20R



NEMA
6-20P

For more information on these and other P&S products refer to our Catalog or visit our web site.

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip® M³ 15 & 20A, 125 & 250V



Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles.
Federal Specification WC596.
CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.
Conforms to NEMA WD-1.

Performance

Electrical

Dielectric Withstand Voltage	1500V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current

Mechanical

Cord Accommodation	Round portable service cords of diameters in accordance with the device rating as defined in UL62
Cord Grip Accommodation	.22" to .66"; 18/3 SV to 12/3 S cord
Terminal Identification	Green Screw = Ground; Brass Screw = Hot; Silver Screw = Neutral
Terminal Accommodation	#18 AWG min. – #12 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration on side

Environmental


Flammability Rating	UL94 HB
Operating Temperatures	Maximum continuous +75°C, minimum -40°C without impact

Materials

Body/Housing	Nylon	Hex Head Ground Screw	Zinc-Plated Steel
Cord Grip Insert	Nylon	Plug Blades	Brass
Terminal Clamp	Brass	Connector Contacts	Brass
Terminal Screws	Nickel- and Brass-Plated Steel	Cord Grip/Assembly Screws	Zinc-Plated Steel

Warranty

1 Year



Dimensions for
MaxGrip® M³ Plug



Dimensions for
MaxGrip® M³ Connector

Complementary Devices & Accessories




STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use




GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



TURNLOCK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Extra-Hard Use Plugs & Connectors
- Heavy-Duty Flanged Inlets & Outlets



TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS



IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- Switches
- Straight Blade Receptacles
- Lighting & Fan Controls
- GFCIs
- Weatherproof Boxes & Covers
- Wall Plates
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF502R2 - Updated March 2008 - For latest specs visit www.legrand.us/passandseymour



Pass & Seymour

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip® M³ 15 & 20A, 125 & 250V

PS5965-Y, PS5965-GRY, PS5965-O, PS5969-Y, PS5969-GRY, PS5969-O,
PS5364-Y, PS5364-GRY, PS5369-Y, PS5369-GRY, PS5666-Y, PS5669-Y,
PS5464-Y, PS5469-Y

Easy assembly and a durable design.

With their tri-drive assembly and terminal screws in addition to self-hinged nylon housings, MaxGrip M³ plugs and connectors install quickly and easily. They stay installed, too — because their rugged construction and high-retention cord grips help them shrug off impacts and constant use.



Features & Benefits

High-visibility yellow and orange, or gray.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

Self-hinge swings wide open to make quick, easy work of tight, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.

PS5965-Y and PS5969-Y

Tough nylon construction with crush/impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.

Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

SF502R2 – Updated March 2008 – For latest specs visit www.legrand.us/passandseymour

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip[®] M³ 15 & 20A, 125 & 250V

Ordering Information

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.
MaxGrip[®] M³ Plugs & Connectors				
PS5965-Y	15 125	Plug, Yellow	.230"-.720"	5-15P
PS5965-GRY	15 125	Plug, Gray	.230"-.720"	5-15P
PS5965-O	15 125	Plug, Orange	.230"-.720"	5-15P
PS5969-Y	15 125	Connector, Yellow	.230"-.720"	5-15R
PS5969-GRY	15 125	Connector, Gray	.230"-.720"	5-15R
PS5969-O	15 125	Connector, Orange	.230"-.720"	5-15R
PS5364-Y	20 125	Plug, Yellow	.230"-.720"	5-20P
PS5364-GRY	20 125	Plug, Gray	.230"-.720"	5-20P
PS5369-Y	20 125	Connector, Yellow	.230"-.720"	5-20R
PS5369-GRY	20 125	Connector, Gray	.230"-.720"	5-20R
PS5666-Y	15 250	Plug, Yellow	.230"-.720"	6-15P
PS5669-Y	15 250	Connector, Yellow	.230"-.720"	6-15R
PS5464-Y	20 250	Plug, Yellow	.230"-.720"	6-20P
PS5469-Y	20 250	Connector, Yellow	.230"-.720"	6-20R



NEMA
5-15R



NEMA
5-15P



NEMA
6-15R



NEMA
6-15P



NEMA
5-20R



NEMA
5-20P



NEMA
6-20R



NEMA
6-20P

For more information on these and other P&S products refer to our Catalog or visit our web site.

Straight Blade Plugs & Connectors Heavy-Duty MaxGrip® M³ 15 & 20A, 125 & 250V



Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles.
Federal Specification WC596.
CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.
Conforms to NEMA WD-1.

Performance


Electrical	
Dielectric Withstand Voltage	1500V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current
Mechanical	
Cord Accommodation	Round portable service cords of diameters in accordance with the device rating as defined in UL62
Cord Grip Accommodation	.22" to .66"; 18/3 SV to 12/3 S cord
Terminal Identification	Green Screw = Ground; Brass Screw = Hot; Silver Screw = Neutral
Terminal Accommodation	#18 AWG min. – #12 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration on side
Environmental	
Flammability Rating	UL94 HB
Operating Temperatures	Maximum continuous +75°C, minimum -40°C without impact

Materials

Body/Housing	Nylon	Hex Head Ground Screw	Zinc-Plated Steel
Cord Grip Insert	Nylon	Plug Blades	Brass
Terminal Clamp	Brass	Connector Contacts	Brass
Terminal Screws	Nickel- and Brass-Plated Steel	Cord Grip/Assembly Screws	Zinc-Plated Steel

Warranty

1 Year



Dimensions for
MaxGrip® M³ Plug



Dimensions for
MaxGrip® M³ Connector

Complementary Devices & Accessories




STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use




GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



TURNLOCK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Extra-Hard Use Plugs & Connectors
- Heavy-Duty Flanged Inlets & Outlets



TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS



IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- Switches
- Straight Blade Receptacles
- Lighting & Fan Controls
- GFCIs
- Weatherproof Boxes & Covers
- Wall Plates
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF502R2 - Updated March 2008 - For latest specs visit www.legrand.us/passandseymour