


# QB2B

Twin 75 watt Quartz Bullet floods come pre-assembled and pre-wired on C103 Mounting plate. Lamps supplied.

Color: Black

Weight: 2.1 lbs



## Lamp Info

Type: T-4  
 Watts: 75W  
 Shape/Size: N/A  
 Base: N/A  
 ANSI: N/A  
 Hours: 1,500  
 Lamp Lumens: 1,500  
 Efficacy: 20 LPW

## Ballast Info

Type: N/A  
 120V: N/A  
 208V: N/A  
 240V: N/A  
 277V: N/A  
 Input Watts: 75W  
 Efficiency: 100%

## Technical Specifications

### UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

### Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

### Lens Gasket:

High temperature silicone gasket stays in place during relamping.

### Reflector:

Semi-specular anodized aluminum.

### Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

### Lens:

Thick, tempered glass.

### Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

### Replacement Lamps:

.

### Installation:

Twin 75w Flood Kit pre-assembled on C103 plate for easy installation.

### Patents:


RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

# QB2B

Twin 75 watt Quartz Bullet floods come pre-assembled and pre-wired on C103 Mounting plate. Lamps supplied.

Color: Black

Weight: 2.1 lbs



## Lamp Info

Type: T-4  
 Watts: 75W  
 Shape/Size: N/A  
 Base: N/A  
 ANSI: N/A  
 Hours: 1,500  
 Lamp Lumens: 1,500  
 Efficacy: 20 LPW

## Ballast Info

Type: N/A  
 120V: N/A  
 208V: N/A  
 240V: N/A  
 277V: N/A  
 Input Watts: 75W  
 Efficiency: 100%

## Technical Specifications

### UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

### Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

### Lens Gasket:

High temperature silicone gasket stays in place during relamping.

### Reflector:

Semi-specular anodized aluminum.

### Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

### Lens:

Thick, tempered glass.

### Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

### Replacement Lamps:

.

### Installation:

Twin 75w Flood Kit pre-assembled on C103 plate for easy installation.

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

**RAB**  
LIGHTING

Tech Help Line: 888 RAB-1000

Email: [sales@rabweb.com](mailto:sales@rabweb.com)

On the web at: [www.rabweb.com](http://www.rabweb.com)

Copyright ©2013 RAB Lighting, Inc. All Rights Reserved

Note: Specifications are subject to change without notice

Page 1 of 1