



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RCD38TRI Radiant SP/3WAY SW+15A TR Outlet Iv

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | RCD38TRI  |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | A Step Up From Ordinary, This Combination Switch and Outlet From The Radiant® Collection Provides Convenience and Flexibility, As Well As Style. Operable In Both Single-Pole and 3-Way Applications, You Can Use It Alone to Control One Light or Fixture, or Use With Another 3-Way Switch For Controlling The Light From Two Locations. Also Includes A Tamper-Resistant Outlet For Safe Access to The Basic Power Every Home Needs. Part Of The Radiant® Collection, It Features Clean Lines and A Smooth Finish For A Soph |
| Weight per unit  | 0.2083 (lbs/each)   |
| Product Category | Gen Purpose Switches  |

### Features

|                       |                     |
|-----------------------|---------------------|
| actuator              | Rocker switch       |
| amperage rating       | 15                  |
| Contact Configuration | 15A                 |
| Contact Rating        | 15 Amp, 120/125 VAC |
| media                 | Yes                 |
| Mounting Type         | Box                 |
| Number of Gangs       | 1.0                 |
| Number of Switches    | 1.0                 |
| operating cycles      | 50000               |
| Poles                 | 1, 3-Way            |
| Switch Type           | Push                |
| Voltage               | 120.0 V             |
| Voltage Rating        | 125                 |
| Wire Size             | #14 - #10 Awg       |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Ivory |
| Finish | Matte |

### Dimensions and Weight

|      |  |
|------|--|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | RADIANT SP/3WAY SW+15A TR OUTLET IV   |
| extra long description | P&S RCD38TRI RADIANT SP/3WAY SW+15A   |
| Features               | Combination, Locator Light  |
| Long Description       | A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a soph |
| Product Type           | Radiant SP/3WAY SW+15A TR Outlet Iv   |
| Special Features       | The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes   |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007055047         |
| Manufacturers Part Number | RCD38TRI               |
| UPC                       | 785007055047           |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | Outlet, Switch     |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 12     |
| Weight Per each | 0.2083 |

## Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Residential   |
| environmental conditions       | UL94 V2   |
| Mounting                       | BOX   |
| Operating Temperature standard | Maximum continuous +115°C, minimum -40°C<br>UL, CULUS, cULus, UL Listed |