



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PTTR63I TR Ehd 20A/125V Iv

*Pass & Seymour/Legrand*

Catalog Number	PTTR63I
Manufacturer	Pass & Seymour/Legrand
Description	Plugtail Registered Industrial Extra Heavy-Duty Spec Grade Tamper-Resistant Receptacles, 20A, 125a
Weight per unit	0.2354 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
Dielectric Strength	Withstands 2000V minimum
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	12

### Dimensions and Weight

Height	3.281
Width	.866

### Descriptions

Description	TR EHD 20A/125V IV
extra long description	P&S PTTR63I TAMPER RESISTANT EHD 20
Long Description	PlugTail Registered Industrial Extra Heavy-Duty Spec Grade Tamper-Resistant Receptacles, 20A, 125A
Product Type	Tamper Resistant Ehd 20A/125V Iv
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007860405
Manufacturers Part Number	PTTR63-I
UPC	785007860405

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	PlugTail™ Tamper-Resistant Spec Grade Receptacle, Extra Heavy-Duty

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.2354

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, cULus UL498, FEDSPEC