



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1038RXL Pan-Term® PV10-38RX-L Loo Panduit Corporation

| | |
|------------------|---|
| Catalog Number | PV1038RXL |
| Manufacturer | Panduit Corporation |
| Description | Ring Terminal, 12 – 10 Awg, 3/8" Stud Size, Vinyl Insulated, Expanded Insulation For Large Wire O.D., Standard Package. |
| Weight per unit | 0.3150 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------------|
| connection | Expanded Entry |
| insulation | Vinyl |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Yellow |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|------|
| Size | 3/8" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | PAN-TERM® PV10-38RX-L LOO |
| extra long description | PAN PV10-38RX-L Pan-Term® PV10-38RX |
| Long Description | Ring Terminal, 12 – 10 AWG, 3/8" stud size, vinyl insulated, expanded insulation for large wire O.D., standard package. |
| Product Type | Pan-Term® PV10-38RX-L Loose Piece Ring Terminal |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983801787 |
| Manufacturers Part Number | PV10-38RX-L |
| UPC | 074983801787 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Ring Terminal |

Packaging

| | |
|-----------------|-------|
| Carton | 50 |
| Package | 500 |
| Weight Per each | 0.315 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure | Ring shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164, CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |