

Eaton QBH1020GF

Catalog Number: QBH1020GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 20A, 22kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB

General specifications



Photo is representative

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton QB GFCI circuit breaker | QBH1020GF |
| UPC | Product Length/Depth |
| 786680222450 | 3.5 in |
| Product Height | Product Width |
| 1.3 in | 6 in |
| Product Weight | Warranty |
| 0.47 lb | 1 year |
| Compliances | Certifications |
| Contact Manufacturer | UL 489 |

Physical Attributes

Circuit breaker type

QB

Connection

Bolt-on

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-4 AWG

Performance Ratings

Amperage Rating

20 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBH1020GF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBH1020GF

Catalog Number: QBH1020GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 20A, 22kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB

General specifications



Photo is representative

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton QB GFCI circuit breaker | QBH1020GF |
| UPC | Product Length/Depth |
| 786680222450 | 3.5 in |
| Product Height | Product Width |
| 1.3 in | 6 in |
| Product Weight | Warranty |
| 0.47 lb | 1 year |
| Compliances | Certifications |
| Contact Manufacturer | UL 489 |

Physical Attributes

Circuit breaker type

QB

Connection

Bolt-on

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-4 AWG

Performance Ratings

Amperage Rating

20 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBH1020GF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)