



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RWC826USBWCCV2 Rad Wireless CHG W 3.1 Usb 15A Rec WH V2 *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | RWC826USBWCCV2 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Radiant® Wireless Charger, Includes Two Traditional Outlets and A Usb Port to Offer Additional Power |
| Weight per unit | 0.5650 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|----------------|---------------------|
| indoor/outdoor | Indoor |
| media | Yes |
| Mounting Type | Box |
| Outlet Type | Indoor, Residential |
| Poles | Double Pole |
| Voltage | 125.0 V |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Descriptions

| | |
|------------------------|--|
| Description | RAD WIRELESS CHG W 3.1 USB 15A REC WH V2 |
| extra long description | P&S RWC826USBWCCV2 RAD WIRELESS CHG |
| Long Description | radiant® Wireless Charger, includes two traditional outlets and a USB port to offer additional power |
| Product Type | Rad Wireless CHG W 3.1 Usb 15A Rec WH V2 |
| Special Features | Wireless Charger |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007133950 |
| Manufacturers Part Number | RWC826USBWCCV2 |
| UPC | 785007133950 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Wire/Plug Strips, Surf Raceways, Power Pole, Walkerduct, & Plugmolds |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 2 |
| Weight Per each | 0.565 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | 95% (relative humidity, non-condensing) |
| nema rating | 15A |
| standard | UL |