Project	Catalog #	Туре	
Prepared by	Notes	Date	



## **RL Retrofit Series**

Recessed LED retrofit module

**Typical Applications** 

Residential

### **Product Certification**











## Product Features



24 Can be u with Title Enclosed

- Available in 3", 4", 5/6" aperture
- 6 selectable color temperature options
  - 2700K, 3000K, 3500K, 4000K, 5000K
  - Dim-to-warm technology included: use your dimmer to warm color temperature from 3000K to 1800K
- · Use with compatible recessed housings
- Dimmable down to 5%

Interactive Menu

• Energy Data page 5

• Dimming Guide


**Top Product Features** 


• Order Information page 2


• Photometric Data page 6 Product Warranty

• Product Specifications page 5

## **Dimensional and Mounting Details**











**IC** 

### **Order Information**

SAMPLE ORDER NUMBER: RL56069FSD2W1EWH

Notes	Notes	Notes	Notes	Notes
retrofit module		with D2W option	cut 5% dimming	flange
RL3 = 3-inch recessed LED	05 = 500 lumens (nominal)	9FSD2W = 90 CRI, selectable CCT	1E = 120V 60Hz, LE & TE phase	WH = matte white
3-inch	Lumens	CRI / CCT	Driver	Finish
3-inch	Lumens	CRI / CCT	Driver	Finish

3-inch Accessories
3-inch Accessories
RL3TRMMW = 3-inch overlay, Matte White RL3TRMMB = 3-inch overlay, Matte Black RL3TRMSN = 3-inch overlay, Satin Nickel RL3TRMTBZ = 3-inch overlay, Tuscan Bronze
Notes

4-inch	Lumens	CRI / CCT	Driver	Finish	4-inch Accessories
4-inch	Lumens	CRI / CCT	Driver	Finish	4-inch Accessories
RL4 = 4-inch recessed LED retrofit module	LS = 600/900 selectable lumens (nominal)	9FSD2W = 90 CRI, selectable CCT with D2W option	1E = 120V 60Hz, LE & TE phase cut 5% dimming	WH = matte white flange	RL4TRMWHB = 4-inch overlay, Matte White, Baffle RL4TRMWBB = 4-inch overlay, Matte Black, Baffle RL4TRMSNB = 4-inch overlay, Satin Nickel, Baffle RL4TRMBBE = 4-inch overlay, Tuscan Bronze, Baffle RL4TRMWH = 4-inch overlay, Matte White, Splay RL4TRMMB = 4-inch overlay, Matte Black, Splay RL4TRMSN = 4-inch overlay, Satin Nickel, Splay RL4TRMSN = 4-inch overlay, Tuscan Bronze, Splay
Notes	Notes	Notes	Notes	Notes	Notes

5/6-inch	Lumens	CRI / CCT	Driver	Finish	5/6-inch Accessories
5/6-inch	Lumens	CRI / CCT	Driver	Finish	5/6-inch Accessories
<b>RL56</b> = 5/6-inch recessed LED retrofit module	06 = 600 lumens (nominal) LS = 900/1200 selectable lumens (nominal)	9FSD2W = 90 CRI, selectable CCT with D2W option	1E = 120V 60Hz, LE & TE phase cut 5% dimming	WH = matte white flange	RL56TRMWHB = 5/6-inch overlay, Matte White, Baffle RL56TRMMBB = 5/6-inch overlay, Matte Black, Baffle RL56TRMSNB = 5/6-inch overlay, Satin Nickel, Baffle RL56TRMBZ = 5/6-inch overlay, Tuscan Bronze, Baffle RL56TRMMB = 5/6-inch overlay, Matte White, Splay RL56TRMMB = 5/6-inch overlay, Matte Black, Splay RL56TRMSN = 5/6-inch overlay, Satin Nickel, Splay RL56TRMSN = 5/6-inch overlay, Tuscan Bronze, Splay
Notes	Notes	Notes	Notes	Notes	Notes



**RL3TRMMW RL4TRMWH RL56TRMWH** White (Paintable), Splay



**RL3TRMSN RL4TRMSN RL56TRMSN** Satin Nickel, Splay



**RL3TRMMB RL4TRMWB** RL56TRMWB Matte Black, Splay



RL3TRMTBZ **RL4TRMTBZ** RL56TRMTBZ Tuscan Bronze, Splay



**RL4TRMWHB RL56TRMWHB** White (Paintable), Baffle



**RL4TRMSNB RL56TRMSNB** Satin Nickel, Baffle



**RL4TRMMBB** RL56TRMMBB Matte Black, Baffle





**RL4TRMTBZB RL56TRMTBZB** Tuscan Bronze, Baffle




## **Dimensional and Mounting Details**









RL4









### **Compatible Housings**

#### HALO - 6" Housings 1

HALO LED	H750ICAT, H750RICAT, H750T, H750TCP, H2750ICAT, H2750RICAT, H550ICAT, H550RICAT, E550ICAT, E550RICAT, E750ICAT, E750RICAT, H750FR2ICAT	
HALO LED Retrofit	ML7BXRFK, ML7E26RFK	
Standard Housing	H7ICAT, H7ICT, H7T, H7ICATNB, H7ICTNB, H7TNB, H7UICAT, H7TCP, H7RICAT, H7RICT, H7RT, E7ICAT, E7ICATNB, E7RICAT, E7RTAT, E7TAT, E7TATNB, H7UICAT, H7ICATNB, H7ICTNB, H7TNB, H7UICAT	
Shallow Housing	H27ICAT, H27RICAT, H27ICT, H27RICT, H27T, H27RT, EI2700AT, EI2700, EI2700R, ET2700, ET2700R, E27ICAT, E27RICAT, E27TAT, E27RTAT	

#### HALO - 5" Housings 1

Halo LED	H550ICAT, H550RICAT, E550ICAT, E550RICAT, H550FR2ICAT
Standard Housing	H5ICAT, H5ICATNB, H5RICAT, H5T, H5TNB, H5RT, E5ICAT, E5ICATNB, E5RICAT, E5RTAT, E5TAT, E5TATNB
Shallow Housing	H25ICAT, H25RICAT, H25ICATNB

#### HALO - 4" Housings<sup>2</sup>

Halo LED	H45ICAT*, H45RICAT*, H450FR2ICAT*
Standard Housing	H99ICAT, H99RTAT, H99TAT, H995ICAT, H995RICAT, H99T, H99RT, H99ICT, E4ICATSB, E4TATSB, E4RTATSB
Shallow Housing	H245ICAT, H245RICAT

#### HALO - 3" Housings <sup>3</sup>

Halo LED	H35ICAT, H35RICAT, H350FR2ICAT
Standard Housing	H36ICAT, H38ICAT, H36TAT, H36RTAT, H36PAR16ICAT, H36PAR16RICAT

#### LUMINAIRES - UL Classified for retrofit compatibility

Note: Compatible with any 5" or 6" diameter recessed luminaire with an internal volume that exceeds 115 in<sup>3</sup> in addition to those listed below.

Juno	Standard Housing	IC22, IC22R, IC22W, IC22S, IC23, IC23W, TC2, TC2R, IC2	
	Shallow Housing	IC21, IC21R	
Conri	Standard Housing	CR1, PR1, QL1	
Capri	Shallow Housing	R9ASIC/PS9RM	
Elco		HL7ICA (EL7ICA)	
Thomas		PS1	
Commercia	al Electric	C7ICA, H3	

Lithonia	Standard Housing	LC6, L7X
Lighting	Shallow Housing	L7XP
Progress	Standard Housing	P87-AT**
Lighting	Shallow Housing	P86TG
Lightolier		1104ICS**, 1104ICR**

1. The RL56 SeleCCTable is UL Certified for use with any 5" or 6" diameter recessed luminaire constructed of steel or aluminum with an internal volume that exceeds 97.4" in<sup>3</sup> addition to those noted below and does not exceed the input rating of the luminaire.

2. The RL4 SeleCCTable is UL Certified for use with any 4" diameter recessed luminaire constructed of steel or aluminum with an internal volume that exceeds 47.8" in<sup>3</sup> addition to those noted below and does not exceed the input rating of the luminaire.

**3.** The RL3 SeleCCTable is UL Certified for use with any 3" diameter recessed luminaire constructed of steel or aluminum with an internal volume that exceeds 42.2" in<sup>3</sup> addition to those noted below and does not exceed the input rating of the luminaire.



## **RL Retrofit Series**

## **Product Specifications**

#### Selectable System

- Use the CCT select switch to choose between D2W, 2700K, 3000K, 3500K, 4000K, and 5000K CCT
- D2W option starts at 3000K and warms to 1800K as fixture dims
- Use the lumen select switch on lumen selectable fixtures to choose brightness level

#### Module – Trim

- Module construction includes LED array, heat sink, reflector, lens, baffle and trim ring
- Regressed baffle
- Heat sink designed to conduct heat away from the LED array, keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments

#### **LED Array**

- Mid power LED array provides a uniform source with high efficiency and no pixilation
- 90 CRI minimum, R9 greater than 50

# Color accuracy at 4 SDCM in between endpoints, provide color accuracy and uniformity.

Color Temperature (CCT) is set to a factory default of 3000K

#### **Optical Assembly**

#### Regressed lens

- Impact-resistant polycarbonate
- Convex form and lamp-like appearance
- Diffuse for even illumination

#### Driver

- Integral 120V 60 Hz constant current driver provides noise free operation
- Continuous, flicker-free dimming from 100% to 5%
- Inline electrical quick connect and E26 adapter (provided) provides mains connections
- See Dimming Guide for compatible dimmers

#### Retention

- For 3-inch and 4-inch: Push-N-Twist universal installation clips are pre-installed and designed to fit compatible recessed housings.
- For 5/6-inch: Torsion springs are pre-installed and adjust to fit 5-inch or 6-inch housings. Push-N-Twist universal installation clips are also included

#### **Overlays (sold separately)**

Overlays are accessory rings that attach to the fixture for a decorative finish. Refer to the accessories table in the ordering information section for details

#### Gaskets

Closed cell gaskets achieve restrictive airflow requirements without additional caulking

#### Compliance

- UL Certified for US and Canada for use with Halo housings, classified for use with other's housings, see instruction sheet for conditions of acceptability
- UL Certified for US and Canada, type IC suitable for direct contact with air permeable insulation
- Not for use in direct contact with spray foam insulation, reference NEMA LSD57-2013
- Wet and Damp location listed
- Airtight certified per ASTM-E283
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- · Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy luminaire compliance. Complies with Title 24 JA8-2022-E.
- Can be used International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- ENERGY STAR® listed, reference database for current listings
- IP44 Ingress Protection rated

#### Warranty

 Five year limited warranty, consult website for details. <u>www.cooperlighting.com/warranty</u>

### **Energy Data**

#### RL3 - 500 Lumen

Lumens	500	
Input Voltage	120V	
Input current	55mA	
Input Power	6.2W	
Efficiency	80.24%	
Inrush(A)	1.58	
THD	13.7	
PF	0.964	
Sound Rating	<=22dba	

#### RL4 - 600/900 Lumen

Lumens	600/900
Input Voltage	120V
Input current	95mA
Input Power	11W
Efficiency	80.56%
Inrush(A)	2.5
THD	16.6
PF	0.983
Sound Rating	<=22dba

#### RL56 - 600 Lumen


Lumens	600
Input Voltage	120V
Input current	60mA
Input Power	6.8W
Efficiency	80.80%
Inrush(A)	2.02
THD	18.9
PF	0.937
Sound Rating	<=22dba

#### RL56 - 900/1200 Lumen

Lumens	900/1200
Input Voltage	120V
Input current	120mA
Input Power	14.5W
Efficiency	80.87%
Inrush(A)	3.8
THD	8.4
PF	0.986
Sound Rating	<=22dba

## **RL Retrofit Series**

### **Photometric Data**




#### RL3059FSD2W1EWH -500LM -3000K

Spacing criterion: (0-180) 1.11 | (90-270) 1.11 | (Diagonal) 1.16 Beam Angle: 83° Field Angle: 132° Lumens: 610 Input Watts: 6.4 W Efficacy: 95.3 LPW UGR: 17 Test Report: P639465

Zonal Lumen	Lumens	% Lumens
0-30	245	40.1
0-40	378	62
0-60	556	91.2
0-90	610	100

TM-30-15	Rf = 93
1101-30-13	Rg = 103
	Ra = 96.6
CRI/CIE	R9 = 89
CCT - Range of	2700K- 5000K
warma 🖌	lcos 🗲






	RL4LS9FSD2W1EWH -600LM -3000K
	Spacing criterion:
	(0-180) 1.15   (90-270) 1.15   (Diagonal) 1.2
	Beam Angle: 86°
)°	Field Angle: 137°
0	Lumens: 695
	Input Watts: 6.9 W
	Efficacy: 100.7 LPW
	UGR: 19
	Test Report: P639470

Zonal Lumen	Lumens	% Lumens
0-30	263	38.4
0-40	412	60.1
0-60	616	89.9
0-90	685	100

Rg = 103
Ra = 96.3
R9 = 85
700K- 5000K





#### **RL4LS9FSD2W1EWH -900LM -3000K** Spacing criterion: (0-180) 1.15 | (90-270) 1.15 | (Diagonal) 1.2 Beam Angle: 86° Field Angle: 137° Lumens: 970 Input Watts: 10.9 W Efficacy: 89 LPW UGR: 20 Test Report: P639475

Zonal Lumen	Lumens	% Lumens
0-30	372	38.4
0-40	583	60.1
0-60	872	89.9
0-90	970	100

TM-30-15	Rf = 92
111-50-15	Rg = 103
CRI/CIE	Ra = 96.3
GRI/GIE	R9 = 85
CCT - Range of	2700K- 5000K
warm 🖌	ltos 🚓

# 86°

#### **Product Specifications**

#### RL3059FSD2W1EWH

PRODUCT SPECIFICATION	NS
Lumens	610
Watts	6.4
Lumens Per Watt (Efficacy)	95.3
Color Accuracy (CRI)	95
Light Color (CCT) Correlated Color Temperature (CCT)	3000K
<b>↓</b>	
warm white soft white bright 2700K 3000K 4500K	white 6500K


#### RL4LS9FSD2W1EWH

PRODUCT SPECIFICATIONS	
Lumens	970
Watts	10.9
Lumens Per Watt (Efficacy)	88.9
Color Accuracy (CRI)	93
Light Color (CCT) Correlated Color Temperature (CCT)	3000K
warm white soft white brig 700K 3000K 4500K	ht white 6500)



## **RL Retrofit Series**

### **Photometric Data**




#### RL56069FSD2W1EWH -600LM -3000K

Spacing criterion: (0-180) 1.21 | (90-270) 1.21 | (Diagonal) 1.3 Beam Angle: 98° Field Angle: 145° Lumens: 700 Input Watts: 6.8 W Efficacy: 102.9 LPW UGR: 19 Test Report: P639490

Zonal Lumen	Lumens	% Lumens
0-30	231	33
0-40	372	53.2
0-60	611	87.3
0-90	700	100

TM-30-15	Rf = 93
1101-30-15	Rg = 103
	Ra = 96.4
CRI/CIE	R9 = 87
CCT - Range of	
warm 🖌	loos 🔶






Spacing criterion:
(0-180) 1.21   (90-270) 1.21   (Diagonal) 1.3
Beam Angle: 98°
Field Angle: 145°
Lumens: 880
Input Watts: 8.5 W
Efficacy: 103.5 LPW
UGR: 20
Test Report: P639500

RL56LS9FSD2W1EWH -900LM -3000K

Zonal Lumen	Lumens	% Lumens
0-30	290	33
0-40	468	53.2
0-60	768	87.3
0-90	880	100

TM-30-15	Rf = 92
1101-50-15	Rg = 103
	Ra = 95.6
CRI/CIE	R9 = 81
CCT - Range of	2700K- 5000K
warre	1001





#### **RL56LS9FSD2W1EWH -1200LM -3000K** Spacing criterion: (0-180) 1.21 | (90-270) 1.21 | (Diagonal) 1.3 Beam Angle: 98° Field Angle: 145° Lumens: 1355 Input Watts: 14.3 W Efficacy: 94.8 LPW UGR: 20 Test Report: P639495

Zonal Lumen	Lumens	% Lumens
0-30	447	33
0-40	721	53.2
0-60	1183	87.3
0-90	1355	100

TM-30-15	Rf = 92
1101-30-13	Rg = 103
	Ra = 95.6
CRI/CIE	R9 = 81
CCT - Range of	2700K- 5000K
warm	<b>cost</b>

# 98°

#### **Product Specifications**

#### RL56069FSD2W1EWH

PRODUCT SPECIFICATIO	NS
Lumens	700
Watts	6.8
Lumens Per Watt (Efficacy)	102.9
Color Accuracy (CRI)	95
Light Color (CCT) Correlated Color Temperature (CCT)	3000K
	a u bita
warm white soft white brigh 2700K 3000K 4500K	t white 6500K

#### RL56LS9FSD2W1EWH

PRODUCT SPECIFICATIONS	
Lumens	1355
Watts	14.3
Lumens Per Watt (Efficacy)	94.7
Color Accuracy (CRI)	93
Light Color (CCT) Correlated Color Temperature (CCT)	3000K
<b>↓</b>	
warm white soft white brigh 700K 3000K 4500K	nt white 65001



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2023 Cooper Lighting Solutions All Rights Reserved.

Specifications and dimensions subject to change without notice.