

Eaton SC-15

Catalog Number: SC-15

Eaton Bussmann series SC fuse, Current-limiting time-delay fuse, Rejection style, 15 A, Class G, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 10 kAIC at 170 Vdc|100 kAIC at 600 Vac, Standard, 600 V, 170 Vdc

General specifications



Product Name	Catalog Number
Eaton Bussmann series SC fuse	SC-15
UPC	EAN
051712250153	5027590066327
Product Length/Depth	Product Height
0.41 in	1.31 in
Product Width	Product Weight
0.41 in	0.1 lb
Warranty	Compliances
Not Applicable	RoHS Compliant CE Marked

Electrical rating

Amperage Rating

15 A

Interrupt rating

100 kAIC at 600 Vac

10 kAIC at 170 Vdc

Response time

12 sec at 200%

Voltage rating

600 Vac, 170 Vdc

Physical details

Packaging type

Standard

General information

Class

Class G

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Rejection style

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - SC-15](#)

Technical data sheets

[SC-15~BUSS SC FUSE CLASS G CLASS G](#)

[Bussmann series SC Class G Fuse Data Sheet No. 1024](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)