


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	BARREL		OVERALL LENGTH "A"	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS					
		I.D. ± .01	O.D. ± .01			CT-700 (OBSOLETE)	CT-1700	CT-720	CT-920/CT-920CH CT-930/CT-930CH CT-940CH CT-950/CT-950CH	CT-980 CT-980CH CT-2950 CT-2990	CT-2001
SCSS8-L	#8 AWG or 23 NAVY	0.18	0.27	1.00	7/16	CD-700-8-2 RED P21 2 CRIMPS	RED P21 2 CRIMPS	CD-720-1 RED P21 1 CRIMP	CD-920-8 RED P21 1 CRIMP	—	CD-2001-8 RED P21 1 CRIMP
SCSS6-L	#6 AWG or 30 NAVY	0.22	0.31	1.00	7/16	CD-700-8-2 BLUE P24 2 CRIMPS	BLUE P24 2 CRIMPS	CD-720-1 BLUE P24 1 CRIMP	CD-920-6 BLUE P24 1 CRIMP	—	CD-2001-6 BLUE P24 1 CRIMP
SCSS4-L	#4 AWG or 40-50 NAVY	0.28	0.38	1.00	7/16	CD-700-8-2 GRAY P29 2 CRIMPS	GRAY P29 2 CRIMPS	CD-720-1 GRAY P29 1 CRIMP	CD-920-4 GRAY P29 1 CRIMP	STD 1 CRIMP	CD-2001-4 GRAY P29 1 CRIMP
SCSS2-0	#2 AWG or 60 NAVY	0.31	0.42	1.25	9/16	CD-700-8-2 BROWN P33 2 CRIMPS	BROWN P33 2 CRIMPS	CD-720-1 BROWN P33 1 CRIMP	CD-920-2 BROWN P33 1 CRIMP	STD 1 CRIMP	CD-2001-2 BROWN P33 1 CRIMP
SCSS1-0	#1 AWG or 75 NAVY	0.36	0.47	1.44	11/16	CD-700-1-1/0 GREEN P37 3 CRIMPS	GREEN P37 3 CRIMPS	CD-720-2 GREEN P37 1 CRIMP	CD-920-1 GREEN P37 1 CRIMP	STD 1 CRIMP	CD-2001-1 GREEN P37 1 CRIMP
SCSS1/0-X	1/0 AWG or 100 NAVY	0.39	0.52	1.44	11/16	CD-700-1-1/0 PINK P42 3 CRIMPS	—	CD-720-2 PINK P42 1 CRIMP	CD-920-1/0 PINK P42 1 CRIMP	STD 1 CRIMP	CD-2001-1/0 PINK P42 1 CRIMP
SCSS2/0-X	2/0 AWG or 125 NAVY	0.45	0.58	1.56	3/4	—	—	CD-720-2 BLACK P45 2 CRIMPS	CD-920-2/0 BLACK P45 1 CRIMP	STD 1 CRIMP	CD-2001-2/0 BLACK P45 2 CRIMPS
SCSS3/0-X	3/0 AWG or 150 NAVY	0.51	0.64	1.69	3/4	—	—	CD-720-2 ORANGE P50 2 CRIMPS	CD-920-3/0 ORANGE P50 1 CRIMP	STD 1 CRIMP	CD-2001-3/0 ORANGE P50 2 CRIMPS
SCSS4/0-X	4/0 AWG or 200 NAVY	0.57	0.71	1.81	13/16	—	—	CD-720-3 PURPLE P54 2 CRIMPS	CD-920-4/0 PURPLE P54 1 CRIMP	STD 1 CRIMP	CD-2001-4/0 PURPLE P54 2 CRIMPS
SCSS250-X	250 MCM 250 NAVY	0.63	0.77	2.19	1-1/16	—	—	CD-720-3 YELLOW P62 2 CRIMPS	CD-920-250 YELLOW P62 1 CRIMP	STD 1 CRIMP	CD-2001-250 YELLOW P62 2 CRIMPS



**NOTES:**

MATERIAL - HIGH CONDUCTIVITY SEAMLESS COPPER TUBING.

ELECTRO-TIN PLATED.

BARREL COLOR CODED WITH DIE SET INDEX NUMBER.

UL LISTED WITH CODE COPPER CONDUCTORS FOR APPLICATIONS UP TO 35KV, FILE E52164.

CONSULT CABLE MANUFACTURER FOR VOLTAGE STRESS RELIEF INSTRUCTIONS WITH APPLICATIONS GREATER THAN 2000 VOLTS.

CSA CERTIFIED FOR APPLICATIONS UP TO 600V, FILE LR31212.

FOR USE WITH COPPER CABLES ONLY.

\*CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER

C41063\_03



LISTED  
587H  
E52164




CERTIFIED  
LR31212

PANDUIT CORP TINLEY PARK, ILL. INDIS											
SCSS #8 THRU 250 COPPER SPLICES											
CUSTOMER DRAWING											
03	4/01	KMD								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: 1.X1 ± .0001 1.XX1 ± .0001 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
02	1-93	WL	GRM					01369	RJM	RS	REVISD NOTES/ADDED TOLERANCES AND CT-980/CT-980CH
01	12-92	WL	GRM					01307	RJM	RS	ADDED CT-2001
00	5-92	WL	GRM					00980		RS	RELEASED
REV	DATE	BY	CHK					ECN	PM	CUST	DESCRIPTION
DRAWING NO. C41063										SCALE N/A	
SEE NOTES ABOVE										DWG'D GRM	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	BARREL		OVERALL LENGTH "A" ± .06	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS					
		I.D. ± .01	O.D. ± .01			CT-700 (OBSOLETE)	CT-1700	CT-720	CT-920/CT-920CH CT-930/CT-930CH CT-940CH CT-950/CT-950CH	CT-980 CT-980CH CT-2950 CT-2990	CT-2001
						DIE PART NO. - DIE SET COLOR & INDEX NO./NUMBER OF CRIMPS					
SCSS8-L	#8 AWG or 23 NAVY	0.18	0.27	1.00	7/16	CD-700-8-2 RED P21 2 CRIMPS	RED P21 2 CRIMPS	CD-720-1 RED P21 1 CRIMP	CD-920-8 RED P21 1 CRIMP	—	CD-2001-8 RED P21 1 CRIMP
SCSS6-L	#6 AWG or 30 NAVY	0.22	0.31	1.00	7/16	CD-700-8-2 BLUE P24 2 CRIMPS	BLUE P24 2 CRIMPS	CD-720-1 BLUE P24 1 CRIMP	CD-920-6 BLUE P24 1 CRIMP	—	CD-2001-6 BLUE P24 1 CRIMP
SCSS4-L	#4 AWG or 40-50 NAVY	0.28	0.38	1.00	7/16	CD-700-8-2 GRAY P29 2 CRIMPS	GRAY P29 2 CRIMPS	CD-720-1 GRAY P29 1 CRIMP	CD-920-4 GRAY P29 1 CRIMP	STD 1 CRIMP	CD-2001-4 GRAY P29 1 CRIMP
SCSS2-0	#2 AWG or 60 NAVY	0.31	0.42	1.25	9/16	CD-700-8-2 BROWN P33 2 CRIMPS	BROWN P33 2 CRIMPS	CD-720-1 BROWN P33 1 CRIMP	CD-920-2 BROWN P33 1 CRIMP	STD 1 CRIMP	CD-2001-2 BROWN P33 1 CRIMP
SCSS1-0	#1 AWG or 75 NAVY	0.36	0.47	1.44	11/16	CD-700-1-1/0 GREEN P37 3 CRIMPS	GREEN P37 3 CRIMPS	CD-720-2 GREEN P37 1 CRIMP	CD-920-1 GREEN P37 1 CRIMP	STD 1 CRIMP	CD-2001-1 GREEN P37 1 CRIMP
SCSS1/0-X	1/0 AWG or 100 NAVY	0.39	0.52	1.44	11/16	CD-700-1-1/0 PINK P42 3 CRIMPS	—	CD-720-2 PINK P42 1 CRIMP	CD-920-1/0 PINK P42 1 CRIMP	STD 1 CRIMP	CD-2001-1/0 PINK P42 1 CRIMP
SCSS2/0-X	2/0 AWG or 125 NAVY	0.45	0.58	1.56	3/4	—	—	CD-720-2 BLACK P45 2 CRIMPS	CD-920-2/0 BLACK P45 1 CRIMP	STD 1 CRIMP	CD-2001-2/0 BLACK P45 2 CRIMPS
SCSS3/0-X	3/0 AWG or 150 NAVY	0.51	0.64	1.69	3/4	—	—	CD-720-2 ORANGE P50 2 CRIMPS	CD-920-3/0 ORANGE P50 1 CRIMP	STD 1 CRIMP	CD-2001-3/0 ORANGE P50 2 CRIMPS
SCSS4/0-X	4/0 AWG or 200 NAVY	0.57	0.71	1.81	13/16	—	—	CD-720-3 PURPLE P54 2 CRIMPS	CD-920-4/0 PURPLE P54 1 CRIMP	STD 1 CRIMP	CD-2001-4/0 PURPLE P54 2 CRIMPS
SCSS250-X	250 MCM 250 NAVY	0.63	0.77	2.19	1-1/16	—	—	CD-720-3 YELLOW P62 2 CRIMPS	CD-920-250 YELLOW P62 1 CRIMP	STD 1 CRIMP	CD-2001-250 YELLOW P62 2 CRIMPS



**NOTES:**

MATERIAL - HIGH CONDUCTIVITY SEAMLESS COPPER TUBING.

ELECTRO-TIN PLATED.

BARREL COLOR CODED WITH DIE SET INDEX NUMBER.

UL LISTED WITH CODE COPPER CONDUCTORS FOR APPLICATIONS UP TO 35KV, FILE E52164.

CONSULT CABLE MANUFACTURER FOR VOLTAGE STRESS RELIEF INSTRUCTIONS WITH APPLICATIONS GREATER THAN 2000 VOLTS.

CSA CERTIFIED FOR APPLICATIONS UP TO 600V, FILE LR31212.

FOR USE WITH COPPER CABLES ONLY.

\*CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER

C41063\_03



LISTED  
587H  
E52164



CERTIFIED  
LR31212

										<b>PANDUIT</b> CORP TINLEY PARK, ILL. INDIS			
										<b>SCSS #8 THRU 250 COPPER SPLICES</b>			
										<b>CUSTOMER DRAWING</b>			
03	4/01	KMD		ADDED LETTER "P" TO DIE NO. REMOVED ALTERNATE DIE INDEX NO. ADDED CT-2940 AND ADAPTER NOTE.								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: 1.X1 ± .0001 1.XX1 ± .0001 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
02	1-93	WL	GRM	REVISED NOTES/ADDED TOLERANCES AND CT-980/CT-980CH						01369	RJM	RS	SCALE N/A
01	12-92	WL	GRM	ADDED CT-2001						01307	RJM	RS	DRAWN BY WL DATE 5-12-92 MATERIAL: SEE NOTES ABOVE
00	5-92	WL	GRM	RELEASED						00980		RS	DRAWING NO. C41063 DDB B
REV	DATE	BY	CHK	DESCRIPTION						ECN	PM	CUST	SIZE