

Project Name

Location

Prepared By



SATCO S29867

4W CFC/LED/50K/CL/120V

Notes

(www) 03-03-2023 09:34:03

General

Status	Discontinued
Substitute	S21299
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	CA11
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	350L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Product Category	Candle
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.9
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.69
MOD	1.38
Weight (lb.)	0.03

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Project Name

Location

Prepared By



SATCO S29867

4W CFC/LED/50K/CL/120V

Notes

(www) 03-03-2023 09:34:03

General

Status	Discontinued
Substitute	S21299
Watts	4W
Incandescent Equivalent	40W
Volts	120V
Shape	CA11
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	350L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Product Category	Candle
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.9
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.69
MOD	1.38
Weight (lb.)	0.03

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp