ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
13405 Stemmons Frwy
Farmers Branch, TX 75234-0
Phone: 9722060016
Fax: 9723522818



S41010CT00 1'' SS304 RIGID CONDUIT, 10' W/COUPLING

CALBRITE

Catalog Number	S41010CT00
Manufacturer	CALBRITE
Description	Rigid Stainless Steel 304 Conduit With Coupling 1" Trade Size 10 Feet Long
Weight per unit	16.1 (lbs/ft)
Product Category	Galvanized Heavy Wall Conduit

Features

Inside Diameter	1.05
Material	Stainless Steel - 304L
Wall Thickness	0.132
Outside Diameter	1.315

Material, Color, and Finish

Color	Stainless Steel
Finish	#4 Polished Finish

Dimensions and Weight

Length	120

Descriptions

Description	1'' SS304 RIGID CONDUIT, 10' W/COUPLING
Features	Stainless conduit is specified in corrosive applications that exceed the limitations of aluminum, fiberglass, rigid steel, PVC, and PVC coated conduit. Type 304 and 316 UL-listed stainless steel conduit meets and exceeds current requirements for wash down and harsh/corrosive environments and satisfies the strictest mandates for plant cleanliness by various state agencies and hundreds of common regulatory requirements.
Long Description	Rigid Stainless Steel 304 Conduit With Coupling 1" Trade Size 10 Feet Long
Product Type	1" X 10' SS304 Conduit W/ Coupling
Short Description	SS_RGD_304
Extra Long Description	CAL S41010CT00 1" X 10' SS304 CONDU

Manufacturer Information

Brand	CALBRITE
	ATKORE - CALBRITE
GTIN	00847656000035
Manufacturers Part Number	S41010CT00
UPC	892933

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
13405 Stemmons Frwy
Farmers Branch, TX 75234-0
Phone: 9722060016
Fax: 9723522818

Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
Type	RIGID

Trade Size

Trade Size	1;27

Availability

Minimum Qty	10

Packaging

Carton	10
Package	50
Weight	1.61
Weight Per Each	16.1 (lbs/ft)

Uses, Certifications, and Standards

Temperature Rating	1600


Atkore™
Calbrite

STAINLESS STEEL RIGID CONDUIT



Features:

- Manufactured in type 304L and 316L stainless steel to meet the demands of any corrosive environment
- Polished with standard “brite” finish to increase corrosion resistance and aesthetic appearance
- Calbrite stainless steel rigid conduit is installed in the same way as any other metallic conduit; there are none of the labor-intensive procedures that come with PVC-coated installations, nor the complicated maintenance and repair procedures
- Standard NPT threads allow for trouble-free installations
- Approx. Heat Tolerance = -150˚F to 1600˚F
- Includes one coupling with each length purchased



Certifications and Compliances:

- UL/cUL 6A Listed
- UL File # E230584
- Article 344, National Electrical Code (NEC)
- CSA C22.1
- Canadian Electrical Code (CEC), Part 1, Standard for Electrical Installations
- NSF/ANSI 169 Certified

Applications:

Stainless conduit is specified in corrosive applications that exceed the limitations of aluminum, fiberglass, rigid steel, PVC, and PVC coated conduit. Calbrite’s Type 304 and 316 UL-listed stainless steel conduit meets and exceeds current requirements for wash down and harsh/ corrosive environments and satisfies the strictest mandates for plant cleanliness by various state agencies and hundreds of common regulatory requirements.

c UL us

Type 304 Part Number	Type 316 Part Number	Trade Size (in)	Outside Diameter (in)	Inside Diameter (in)	Threads per inch	Length w/o Coupling (ft in)	Weight per feet (lb)
S40510CT00	S60510CT00	½	0.840	0.622	14	9' 11¼	0.820
S40710CT00	S60710CT00	¾	1.050	0.824	14	9' 11¼	1.090
S41010CT00	S61010CT00	1	1.315	1.049	11.5	9' 11	1.610
S41210CT00	S61210CT00	1¼	1.660	1.380	11.5	9' 11	2.180
S41510CT00	S61510CT00	1½	1.900	1.610	11.5	9' 11	2.630
S42010CT00	S62010CT00	2	2.375	2.067	11.5	9' 11	3.500
S42510CT00	S62510CT00	2½	2.875	2.469	8	9' 10½	5.590
S43010CT00	S63010CT00	3	3.500	3.068	8	9' 10½	7.270
S44010CT00	S64010CT00	4	4.500	4.026	8	9' 10¼	10.080

All dimensions are for informational purposes only *Tolerances +/- 5%