

# Specifications

Photo is representative



## Eaton S811+R10N3S

Eaton S811+ soft starter, 1000 A, R-frame, Three-pole, 24 V power, 200-600 V operating voltage, 47-63 Hz, 1-2 conductors, #22-14 AWG wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

### General specifications

<b>PRODUCT NAME</b>	Eaton S811+ soft starter
<b>CATALOG NUMBER</b>	S811+R10N3S
<b>UPC</b>	786685558936
<b>PRODUCT LENGTH/DEPTH</b>	6.64 in
<b>PRODUCT HEIGHT</b>	7.92 in
<b>PRODUCT WIDTH</b>	4.38 in
<b>PRODUCT WEIGHT</b>	10.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	CSA file No. 3211-06 UL Recognized EN 60947-4-2 IEC 60947-4-2 UL Listed CSA Certified for Elevator Duty
<b>CATALOG NOTES</b>	All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification.

### Product specifications

<b>USED WITH</b>	Three-phase motors
<b>AMPERAGE RATING</b>	1000A
<b>DISPLAY MATERIAL</b>	LCD
<b>AC CURRENT - MAX</b>	240 Vac
<b>DC CURRENT - MAX</b>	120 Vdc
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Soft starter

### Resources

<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a>
<b>MULTIMEDIA</b>	<a href="#">Soft Starter Product Family Overview</a> <a href="#">Soft starter DS7 up to 200 A</a> <a href="#">Soft Starter DS7 up to 32 A</a>

<b>FREQUENCY RATING</b>	47-63 Hz
<b>POWER SUPPLY</b>	24 V
<b>FRAME SIZE</b>	R
<b>OPERATING TEMPERATURE - MAX</b>	50 °C
<b>COMMUNICATION</b>	Modbus RTU
<b>NEMA RATING</b>	NEMA 0
<b>SIZE</b>	NEMA 0
<b>OPERATING VOLTAGE</b>	200-600 V
<b>WIRE SIZE</b>	#22-14 AWG
<b>MODULE INTERFACE</b>	Digital interface module
<b>OPERATING TEMPERATURE - MIN</b>	-30 °C

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - S811+R10N3S](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

Photo is representative



## Eaton S811+R10N3S

Eaton S811+ soft starter, 1000 A, R-frame, Three-pole, 24 V power, 200-600 V operating voltage, 47-63 Hz, 1-2 conductors, #22-14 AWG wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

### General specifications

<b>PRODUCT NAME</b>	Eaton S811+ soft starter
<b>CATALOG NUMBER</b>	S811+R10N3S
<b>UPC</b>	786685558936
<b>PRODUCT LENGTH/DEPTH</b>	6.64 in
<b>PRODUCT HEIGHT</b>	7.92 in
<b>PRODUCT WIDTH</b>	4.38 in
<b>PRODUCT WEIGHT</b>	10.5 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	CSA file No. 3211-06 UL Recognized EN 60947-4-2 IEC 60947-4-2 UL Listed CSA Certified for Elevator Duty
<b>CATALOG NOTES</b>	All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification.

### Product specifications

<b>USED WITH</b>	Three-phase motors
<b>AMPERAGE RATING</b>	1000A
<b>DISPLAY MATERIAL</b>	LCD
<b>AC CURRENT - MAX</b>	240 Vac
<b>DC CURRENT - MAX</b>	120 Vdc
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Soft starter

### Resources

<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a>
<b>MULTIMEDIA</b>	<a href="#">Soft Starter Product Family Overview</a> <a href="#">Soft starter DS7 up to 200 A</a> <a href="#">Soft Starter DS7 up to 32 A</a>

<b>FREQUENCY RATING</b>	47-63 Hz
<b>POWER SUPPLY</b>	24 V
<b>FRAME SIZE</b>	R
<b>OPERATING TEMPERATURE - MAX</b>	50 °C
<b>COMMUNICATION</b>	Modbus RTU
<b>NEMA RATING</b>	NEMA 0
<b>SIZE</b>	NEMA 0
<b>OPERATING VOLTAGE</b>	200-600 V
<b>WIRE SIZE</b>	#22-14 AWG
<b>MODULE INTERFACE</b>	Digital interface module
<b>OPERATING TEMPERATURE - MIN</b>	-30 °C

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - S811+R10N3S](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

