

Specifications



Photo is representative



Eaton S811+R13N3S

Eaton S811+ soft starter, 135 A, R-frame, Three-pole, 24 V power, -30°C to -50°C, 200-600 V operating voltage, 47 -63 Hz, 1-2 conductors, #14-4/0 AWG wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton S811+ soft starter |
| CATALOG NUMBER | S811+R13N3S |
| UPC | 786685558943 |
| PRODUCT LENGTH/DEPTH | 6.64 in |
| PRODUCT HEIGHT | 7.92 in |
| PRODUCT WIDTH | 4.38 in |
| PRODUCT WEIGHT | 7 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | CE Marked |
| CERTIFICATIONS | UL Recognized EN 60947-4-2 IEC 60947-4-2 UL Listed CSA file No. 3211-06 CSA Certified for Elevator Duty |
| CATALOG NOTES | All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification. |



Powering Business Worldwide

Product specifications

| | |
|-----------------------------|--------------------------|
| USED WITH | Three-phase motors |
| AMPERAGE RATING | 135A |
| DISPLAY MATERIAL | LCD |
| AC CURRENT - MAX | 240 Vac |
| DC CURRENT - MAX | 120 Vdc |
| NUMBER OF POLES | Three-pole |
| TYPE | Soft starter |
| FREQUENCY RATING | 47-63 Hz |
| POWER SUPPLY | 24 V |
| FRAME SIZE | R |
| OPERATING TEMPERATURE - MAX | 50 °C |
| COMMUNICATION | Modbus RTU |
| NEMA RATING | NEMA 0 |
| SIZE | NEMA 0 |
| OPERATING VOLTAGE | 200-600 V |
| WIRE SIZE | #14-4/0 AWG |
| MODULE INTERFACE | Digital interface module |
| OPERATING TEMPERATURE - MIN | -30 °C |

Resources

| | |
|-------------------------------|--|
| APPLICATION NOTES | S8x1 adjustment - Switching from S801+ to S811+ |
| CATALOGS | Product Range Catalog Drives Engineering Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1 Soft Starter Product Family Overview |
| MULTIMEDIA | Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S811+R13N3S |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton S811+R13N3S

Eaton S811+ soft starter, 135 A, R-frame, Three-pole, 24 V power, -30°C to -50°C, 200-600 V operating voltage, 47 -63 Hz, 1-2 conductors, #14-4/0 AWG wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton S811+ soft starter |
| CATALOG NUMBER | S811+R13N3S |
| UPC | 786685558943 |
| PRODUCT LENGTH/DEPTH | 6.64 in |
| PRODUCT HEIGHT | 7.92 in |
| PRODUCT WIDTH | 4.38 in |
| PRODUCT WEIGHT | 7 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | CE Marked |
| CERTIFICATIONS | UL Recognized EN 60947-4-2 IEC 60947-4-2 UL Listed CSA file No. 3211-06 CSA Certified for Elevator Duty |
| CATALOG NOTES | All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification. |



Powering Business Worldwide

Product specifications

| | |
|-----------------------------|--------------------------|
| USED WITH | Three-phase motors |
| AMPERAGE RATING | 135A |
| DISPLAY MATERIAL | LCD |
| AC CURRENT - MAX | 240 Vac |
| DC CURRENT - MAX | 120 Vdc |
| NUMBER OF POLES | Three-pole |
| TYPE | Soft starter |
| FREQUENCY RATING | 47-63 Hz |
| POWER SUPPLY | 24 V |
| FRAME SIZE | R |
| OPERATING TEMPERATURE - MAX | 50 °C |
| COMMUNICATION | Modbus RTU |
| NEMA RATING | NEMA 0 |
| SIZE | NEMA 0 |
| OPERATING VOLTAGE | 200-600 V |
| WIRE SIZE | #14-4/0 AWG |
| MODULE INTERFACE | Digital interface module |
| OPERATING TEMPERATURE - MIN | -30 °C |

Resources

| | |
|-------------------------------|--|
| APPLICATION NOTES | S8x1 adjustment - Switching from S801+ to S811+ |
| CATALOGS | Product Range Catalog Drives Engineering Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1 Soft Starter Product Family Overview |
| MULTIMEDIA | Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S811+R13N3S |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

