



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T2535183S 25KVA 1PH 480/240 Dry Type Transformer

Acme Electric

Catalog Number	T2535183S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kva
Weight per unit	260.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

Fuse Rating	Primary: 150 AMP For 240 V, 70 AMP For 480 V, Secondary: 300 AMP For 120 V
pallet quantity	4
Primary Voltage	240 x 480 V
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V

Dimensions and Weight

Height	18.44
Length	13.34
Width	16.13

Descriptions

Construction	ENCAPSULATED
Description	25KVA 1PH 480/240 DRY TYPE TRANSFORMER
extra long description	ACME T2535183S TFMR 1PH 25KVA 240X4
Long Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503734209
Manufacturers Part Number	T2535183S
UPC	047503734209



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Distribution Transformer

Packaging

Carton	1
Weight Per each	260

Uses, Certifications, and Standards

Enclosure	NEMA 3R Steel
Frequency Rating	60
Mounting standard	WALL UL 506, UL File Number E79947V1, UL Control Number 50B8, UL Insulation Number H3221, CSA Certified, OSHA Compliant, ANSI, IEEE
Temperature Rating	115 DEG C Rise