



SAFETY DATA SHEET

1. Identification

Product identifier	Thread Lubricant
Other means of identification	
Product code	SL35924, SL35925
Recommended use	General purpose thread lubricant
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufactured or sold by:	
Company name	CRC Industries, Inc.
Address	885 Louis Dr. Warminster, PA 18974 US
Telephone	
General Information	215-674-4300
Technical Assistance	800-521-3168
Customer Service	800-272-4620
24-Hour Emergency (CHEMTREC)	800-424-9300 (US) 703-527-3887 (International)
Website	www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	Not available.
Hazard statement	The mixture does not meet the criteria for classification.
Precautionary statement	
Prevention	Observe good industrial hygiene practices.
Response	Wash hands after handling.
Storage	Store away from incompatible materials.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Distillates (petroleum), hydrotreated heavy naphthenic		64742-52-5	90 - 100

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a physician if symptoms develop or persist.
Skin contact	Wash off with plenty of water. Get medical attention if irritation develops and persists.

Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. If ingestion of a large amount does occur, call a poison control center immediately.
Most important symptoms/effects, acute and delayed	None known.
Indication of immediate medical attention and special treatment needed	Treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	Move containers from fire area if you can do so without risk.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	The product is immiscible with water and will spread on the water surface. Stop the flow of material, if this is without risk. Sweep up or vacuum up spillage and collect in suitable container for disposal. Following product recovery, flush area with water. For waste disposal, see section 13 of the SDS. Prevent entry into waterways, sewer, basements or confined areas.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.

7. Handling and storage

Precautions for safe handling	Avoid contact with eyes, skin, and clothing. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices. Use care in handling/storage. For product usage instructions, please see the product label.
Conditions for safe storage, including any incompatibilities	Keep container tightly closed. Store away from incompatible materials (see Section 10 of the SDS). Store in a cool, dry place out of direct sunlight. Store in a well-ventilated place.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Distillates (petroleum), hydrotreated heavy naphthenic (CAS 64742-52-5)	PEL	5 mg/m ³	Mist.
		2000 mg/m ³ 500 ppm	

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Distillates (petroleum), hydrotreated heavy naphthenic (CAS 64742-52-5)	TWA	5 mg/m ³	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Distillates (petroleum), hydrotreated heavy naphthenic (CAS 64742-52-5)	Ceiling	1800 mg/m ³	
	STEL	10 mg/m ³	Mist.
	TWA	5 mg/m ³	Mist.
Biological limit values	No biological exposure limits noted for the ingredient(s).		
Exposure guidelines	Occupational Exposure Limits are not relevant to the current physical form of the product.		
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.		
Individual protection measures, such as personal protective equipment			
Eye/face protection	Wear safety glasses with side shields (or goggles).		
Skin protection			
Hand protection	Wear protective gloves such as: Neoprene. Nitrile.		
Other	Wear suitable protective clothing.		
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.		
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.		
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.		

9. Physical and chemical properties**Appearance**

Physical state	Solid.
Form	Grease.
Color	Amber.
Odor	Mild petroleum.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	680 °F (360 °C) estimated
Flash point	334 °F (167.8 °C) Cleveland Open Cup
Evaporation rate	Very slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapor pressure	0.00001 hPa estimated
Vapor density	> 5 (air = 1)
Relative density	0.9
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	500 °F (260 °C) estimated
Decomposition temperature	Not available.

Viscosity (kinematic)	Not available.
Percent volatile	> 87 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Expected to be a low ingestion hazard.
Inhalation	Health injuries are not known or expected under normal use.
Skin contact	Prolonged skin contact may cause temporary irritation.
Eye contact	Direct contact with eyes may cause temporary irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Prolonged or excessive inhalation may cause respiratory tract irritation.

Information on toxicological effects

Acute toxicity Not available.

Product	Species	Test Results
Thread Lubricant		
Acute		
<i>Dermal</i>		
LD50	Rabbit	2150.5376 mg/kg estimated
<i>Oral</i>		
LD50	Rat	5376.3442 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
Respiratory sensitization	Not available.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not likely, due to the form of the product.
Further information	This product has no known adverse effect on human health.

12. Ecological information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
--------------------	--

Product	Species		Test Results
Thread Lubricant			
Aquatic			
Crustacea	EC50	Daphnia	1075.2688 mg/l, 48 hours estimated
Fish	LC50	Fish	5376.3442 mg/l, 96 hours estimated
Components	Species		Test Results
Distillates (petroleum), hydrotreated heavy naphthenic (CAS 64742-52-5)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	1000 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	5000 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability	Not readily biodegradable.
Bioaccumulative potential	No data available.
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.

15. Regulatory information

US federal regulations	This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200. All components are on the U.S. EPA TSCA Inventory List.
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)	Not regulated.
SARA 304 Emergency release notification	Not regulated.
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	Not listed.
US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance	Not listed.
CERCLA Hazardous Substance List (40 CFR 302.4)	Not listed.
CERCLA Hazardous Substances: Reportable quantity	Not listed. Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.
Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List	Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.**Food and Drug Administration (FDA)** Not regulated.**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

Section 311/312 Hazard categories Immediate Hazard - No
 Delayed Hazard - No
 Fire Hazard - No
 Pressure Hazard - No
 Reactivity Hazard - No

SARA 302 Extremely hazardous substance No**US state regulations****US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)**

Not listed.

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

None.

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

None.

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 100 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** Not regulated**VOC content (CA)** < 0.1 %**VOC content (OTC)** < 0.1 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 01-14-2015
Prepared by Allison Cho
Version # 01
Further information Not available.
HMIS® ratings Health: 1
Flammability: 1
Physical hazard: 0
Personal protection: B
NFPA ratings Health: 1
Flammability: 1
Instability: 0

NFPA ratings



Disclaimer

CRC cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.