




Vinyl Splice For 16 - 14 AWG

By Burndy
Catalog # [SP14](#)

Copper Splice, 16-14 AWG, 1" Splice Length, Vinyl Insulated.



Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810712016
UPC 12 Digit	7818107120166

Dimensions

Cable Insulation Diameter Maximum	0.180 in
Dimension - Diameter Max Size inch	0.18 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.18 in
Dimension - Strip Length inch	1/4 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG
Conductor Size	16 - 14 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[3D Models - SP14_MODEL-PDF](#)
[3D Models - SP14_MODEL-IGES](#)
[3D Models - SP14_MODEL-STEP](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094190](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-SP14-SPEC-EN | REV 8/2023