

## 6" INCANDESCENT

### WHY DBX?

The DBX downlight is AirShield™ rated when used with any compatible trim and is dual rated for IC and Non-IC applications. It can be used in spaces with or without insulation. Refer to trims for lamp and wattage guidelines. The DBX will accommodate a wide variety of trims such as open, shower, baffle, and wall wash.

The DBXMRI<sup>1</sup> is a non-ferrous housing for use in rooms containing magnetic resonance imaging equipment.

### APPLICATIONS

The DBX is ideal for cost conscious applications that require a wide selection of trims for accent, ambient, and wet location illumination. The DBX housing features AirShield, which virtually eliminates air flow between the housing and ceiling cavity.

### OPTIONAL WIRING QUICK-CONNECTS

DBX-QC housing available with all of the great features and trim choices of DBX but with wiring quick-connects for even easier installation.

### TECHNICAL SPECIFICATIONS

#### Dimensions:

**Height:** 7-1/2" (191mm) **Width:** 7-7/8" (200mm) **Length:** 10-3/4" (273mm)  
**Ceiling Cutout:** 6-7/8" (175mm) **Maximum Ceiling Thickness:** 2-1/2" (64mm)

**Voltage:**  
120V

#### Listings:

UL and CUL, IC/Non-IC, damp location listed. Wet location listed when used with certain trims. AirShield™ rated in compliance with ASTM E283 and the Washington State Energy Code (WSEC).

#### Electrical/Installation:

Feed through wiring (4 in, 4 out), integral Romex clamp, toolless adjustment for various ceiling thicknesses, and slotted interlocking bar hangers that span 24".

<sup>1</sup>Only trims TB60, TBW60, TB61, TBW61, TB62, TBW62, T06, T060B, T060C, T060G available for the DBXMRI.

### DBX/DBXQC/ DBXMRI<sup>1</sup>



**6" INCANDESCENT  
AIRSHIELD™ RATED  
IC/NON-IC DUAL RATED  
NEW CONSTRUCTION**



DBX is AirShield™ rated regardless of trim type and without the need for additional gaskets or factory kits.

#### BAFFLE (PAGE 12)

TB60

TBW60

TB61

TBW61

TB62

TBW62

#### OPEN (PAGE 12-13)

T06

T060(B)(C)(G)

T061

T062

#### OPEN SHOWER (PAGE 13-14)

T063WL

T064WL

#### LENSED (PAGE 14-15)

TL60

TL61

TL62

TL63

TL64

#### ADJUSTABLE (PAGE 16)

TA60

TA65

TAW65

#### WALL WASH (PAGE 16)

TW61WBF

TW61BF

### DBX/DBXQC/DBXMRI<sup>1</sup>



**TRIMS**





## 6" INCANDESCENT

### RMNICD

6" INCANDESCENT  
IC/NON-IC DUAL RATED  
REMODEL CONSTRUCTION →



### WHY RMNICD?

The RMNICD has been specifically designed for quick and easy installation into existing ceiling applications.

### APPLICATIONS

The RMNICD is dual rated for spaces with or without insulation contact. Refer to trims for lamp and wattage guidelines. The RMNICD has a wide variety of trims to meet your lighting needs. RMNICD is not AirShield™ rated. Use DBX for air tight housing applications.

### TECHNICAL SPECIFICATIONS

#### Dimensions:

**Height:** 7-1/2" (191 mm) **Width:** 6-5/8" (168mm) **Length:** 15-3/8" (391mm)

**Ceiling Cutout:** 6-5/8" (168mm) **Maximum Ceiling Thickness:** 11/2" (38 mm)

#### Voltage:

120V

#### Listings:

UL and CUL damp location listed. Wet location when used with certain trims.

#### Electrical/Installation:

Feed through wiring (2 in, 2 out) rated for 60° supply wires in end of run applications, and slide bars permit quick and solid mounting in ceilings.

### RMNICD

TRIMS →



#### BAFFLE (PAGE 12)

TB60

TBW60

TB61

TBW61

TB62

TBW62

#### OPEN (PAGE 12-13)

T06

T060(B)(C)(G)

T061

T062

#### OPEN SHOWER (PAGE 13-14)

T063WL

T064WL

#### LENSED (PAGE 14-15)

TL60

TL61

TL62

TL63

TL64

#### ADJUSTABLE (PAGE 16)

TA60

TA65

TAW65

#### WALL WASH (PAGE 16)

TW61WBF

TW61BF




## 6" DBX/RMNICD TRIMS


### BAFFLE




**TB60\***  
**TBW60\***  
Stepped black (TB60) or white (TBW60) baffle. Metal flange.




TB60





**IC LAMP:**  
75W PAR30,  
65W BR30




**NON-IC LAMP:**  
150W PAR38,  
120W BR40,  
40W A19



**TB61\***  
**TBW61\***  
Stepped long-neck black (TB61) or white (TBW61) baffle. Metal flange.





**IC LAMP:**  
75W PAR30,  
65W BR30




**NON-IC LAMP:**  
150W PAR38,  
120W BR40,  
40W A19



**TB62\***  
**TBW62\***  
(TB62) High wattage black stepped baffle.  
(TBW62) High wattage white stepped baffle.



**IC LAMP:**  
90W PAR38,  
90W BR40





**NON-IC LAMP:**  
150W PAR38,  
120W BR40


### OPEN



**T06\***  
White cone with metal flange.



**IC LAMP:**  
75W PAR30,  
65W BR30



**NON-IC LAMP:**  
150W PAR38,  
120W BR40,  
40W A19

\*These trims also available for the DBXMRI.



## 6" COMPACT FLUORESCENT

### WHY IBXICAT?

The IBXICAT housings are Energy Star approved, AirShield™ rated downlights for use with 13W, 18W, 26W quad or triple tube compact fluorescent lamps. The IBX26ICATDM is dimmable to 15% of lamp output and uses standard 2-wire controls. All versions come with Pro-Nail™ bar hangers. Because CFL lamps are compact in size and deliver good lumen output, they are ideal for downlighting applications that require energy efficiency and low maintenance such as residential, retail, commercial, and hospitality spaces.

### APPLICATIONS

The IBXICAT housings may be used in insulated ceilings. Specify the IBXICAT housings in offices, retail stores, restaurant, and hospitality spaces, and residentially in kitchens, closets, and bathrooms.

### TECHNICAL SPECIFICATIONS

#### Dimensions:

**Height:** 7-1/2" (191 mm) **Width:** 7-7/8" (200mm) **Length:** 10-3/4" (330mm)

**Ceiling Cutout:** 6-7/8" (175mm) **Maximum Ceiling Thickness:** 2" (51 mm)

#### Voltage:

120V

#### Listings:

UL and CUL listed for damp locations. Wet location listed when used with certain trims. Thermally protected. AirShield rated. Washington State Energy Code (WSEC) compliant. Meets energy star requirements (IBX18ICAT does not meet Energy Star requirements.)

#### Electrical/Installation:

Feed through wiring (4 in, 4 out), integral Romex clamps, integral nailers and T-bar mounting clamps, socket mounts to trim for consistent lamp position.

**IBX13ICAT**  
**IBX18ICAT**  
**IBX26ICAT**  
**IBX26ICATDM**



**6" FLUORESCENT**  
**ENERGY STAR**  
**AIRSHIELD™ RATED**  
**NEW CONSTRUCTION**



IBXICAT is AirShield™ rated regardless of trim type and without the need for additional gaskets or factory kits.

#### BAFFLE (PAGE 18)

**TB60**

**TBW60**

**TB61**

**TBW61**

**TB62**

**TBW62**

#### OPEN (PAGE 18-19)

**T06**

**T060(B)(C)(G)**

**T061**

**T062**

#### LENSED (PAGE 20-21)

**TL60**

**TL61**

**TL62**

**TL63**

**TL64**

#### WALL WASH (PAGE 21)

**TW61BF**

**TW61WBF**


## IBXICAT

### TRIMS




## 6" IBXICAT TRIMS


### BAFFLE




**TB60**  
**TBW60**  
Stepped black (TB60) or white (TBW60) baffle. Metal flange.



**TB60**




**TBW60**




**IC LAMP:** One 13W Quad Tube or Triple Tube, One 18W Quad or Triple Tube, One 26W Quad or Triple Tube




**TB61**  
**TBW61**  
(TB61) Splay black baffle or (TBW61) splay white baffle. Metal flange.



**TB61**




**TBW61**




**IC LAMP:** One 13W Quad Tube or Triple Tube, One 18W Quad or Triple Tube, One 26W Quad or Triple Tube




**TB62**  
**TBW62**  
(TB62) High wattage black stepped baffle. (TBW62) High wattage white stepped baffle.



**TB62**



**TBW62**





**IC LAMP:** One 13W Quad Tube or Triple Tube, One 18W Quad or Triple Tube, One 26W Quad or Triple Tube

### OPEN



**T06**  
White cone with metal flange.



**IC LAMP:** One 13W Quad Tube or Triple Tube, One 18W Quad or Triple Tube, One 26W Quad or Triple Tube

## 6" HIGH WATTAGE INCANDESCENT

### IBXHW

6" HIGH WATTAGE  
INCANDESCENT  
AIRSHIELD™ RATED  
IC RATED  
NEW CONSTRUCTION



IBXHW is AirShield™ rated regardless of trim type and without the need for additional gaskets or factory kits.

### WHY IBXHW?

The IBXHW downlight is AirShield™ and IC rated. The IBXHW will accommodate a wide variety of trims such as open, shower, baffle, wall wash, and lensed.

### APPLICATIONS

The IBXHW is ideal for applications that require high wattage lamps in insulated ceilings. The IBXHW housing are AirShield™ rated, which virtually eliminates air flow between the ceiling cavity and the housing.

### TECHNICAL SPECIFICATIONS

#### Dimensions:

**Height:** 7-5/8" (194mm) **Width:** 8-3/8" (213mm) **Length:** 13" (330mm)

**Ceiling Cutout:** 6-7/8" (175mm) **Maximum Ceiling Thickness:** 2" (50mm)

#### Voltage:

120V

#### Listings:

UL and CUL damp location listed. Wet location when used with certain trims. AirShield™ rated in compliance with ASTM E283 and the Washington State Energy Code (WSEC).

#### Electrical/Installation:

Feed through wiring (4 in, 4 out), integral romex clamp, integral nailer and T-bar mounting clamp, socket mounts to trim for consistent lamp position.

### IBXHW

TRIMS



#### BAFFLE (PAGE 27)

TB60

TBW60

TB61

TBW61

TB62

TBW62

#### OPEN (PAGE 27-28)

T06

T060(B)(C)(G)

T061

T062

#### OPEN SHOWER (PAGE 28-29)

T063WL

T064WL

#### LENSED (PAGE 29-30)

TL60

TL61

TL62

TL63

TL64

#### ADJUSTABLE (PAGE 30-31)

TA60

TA65

TAW65


#### WALL WASH (PAGE 31)

TW61BF


TW61WBF

## 6" IBXHW TRIMS

### BAFFLE




**IC LAMP:**  
150W PAR38,  
120W BR40,  
100W A19




**TB60**

**TB60**  
**TBW60**

Stepped black (TB60)  
or white (TBW60)  
baffle. Metal flange.





**IC LAMP:**  
75W PAR30L,  
75W BR30,  
75W A19




**TB61**  
**TBW61**

Black (TB61) or white  
(TBW61) stepped  
baffle. Metal flange.



**IC LAMP:**  
150W PAR38,  
120W BR40




**TB62**  
**TBW62**


Stepped black (TB62)  
or white (TBW62)  
baffle. Metal flange.



### OPEN



**IC LAMP:**  
150W PAR38,  
120W BR40,  
100W A19



**T06**

White cone with  
metal flange.



## LITEBOX HOUSING AND TRIM MATRIX

### 6" HOUSINGS AND TRIMS

TRIM TYPE, CATALOG NUMBER, DESCRIPTION			MAXIMUM WATTAGES BY HOUSING							
			HOUSING:		DBX	IBXICAT	IBXHW	IBXS	RMNICS	RMNICD
			TYPE:		IC	NON-IC	IC	IC	IC/NON-IC	IC/NON-IC
ADJUSTABLE	TA60	WHITE EYEBALL	75W PAR30 65W BR30		N/A	75W PAR30 85W BR30	N/A	N/A	75W PAR30 65W BR30	
	TA65	WHITE EYEBALL	50W PAR30 65W BR30	75W PAR30 85W BR30	N/A	75W PAR30 85W BR30	N/A	N/A	50W PAR30 65W BR30	75W PAR30 85W BR30
	TA61	WHITE EYEBALL	N/A	N/A	N/A	N/A	75W PAR30 65W BR30	75W PAR30 65W BR30	N/A	N/A
BAFFLE	TB60 TBW60	STEPPED BLACK (TB60) OR WHITE (TBW60) BAFFLE	75W PAR30 65W BR30	150W PAR30 120W BR40 40W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	150W PAR30 120W BR40 100W A19	N/A	N/A	75W PAR30 65W BR30	150W PAR30 120W BR40 40W A19
	TB61 TBW61	STEPPED BLACK (TB61) OR WHITE (TBW61) BAFFLE	75W PAR30 65W BR30	75W PAR30L 85W BR30 100W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	75W PAR30 75W BR30 75W A19	N/A	N/A	75W PAR30L 65W BR30	75W PAR30L 85W BR30 100W A19
	TB62 TBW62	STEPPED BLACK (TB62) OR WHITE (TBW62) BAFFLE	90W PAR38 65W BR30	150W PAR38 120W BR40	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	150W PAR38 120W BR40	N/A	N/A	90W PAR38 90W BR40	150W PAR38 120W BR40
	TB63 TBW63	STEPPED BLACK (TB63) OR WHITE (TBW63) BAFFLE	N/A	N/A	N/A	N/A	75W PAR30 65W BR30	75W PAR30 65W BR30	N/A	N/A
LENSED AND OPEN WET (wet location listed)	TL60	DROP OPAL SHOWER TRIM (1)TBW62	50W PAR30 40W A19	75W PAR30 75W A19	13W,18W QUAD TUBE/13W, 18W TRIPLE TUBE	75W PAR30 60W A19	N/A	N/A	50W PAR30 40W A19	N/A
	TL61	GLASS DROP OPAL SHOWER TRIM	50W PAR30 100W A19	75W PAR30 100W A19	13W,18W QUAD TUBE/13W, 18W TRIPLE TUBE	75W PAR30 75W A19	N/A	N/A	50W PAR30 100W A19	N/A
	TL62	FRESNEL SHOWER TRIM (1)	50W PAR30	75W PAR30	N/A	75W PAR30	N/A	N/A	50W PAR30	N/A
	TL63	DOMED POLYCARBONATE SHOWER TRIM (1)	40W A19	75W A19	13,18W TRIPLE TUBE/13W QUAD TUBE	60W A19	N/A	N/A	40W A19	N/A
	TL64	WHITE ABALITE FLUSH GLASS SHOWER TRIM	N/A	75W PAR30 60W A19	13,18W TRIPLE TUBE/13W QUAD TUBE	40W A19	N/A	N/A	N/A	75W PAR30 60W A19
	TL66	GLASS DROP OPAL SHOWER TRIM (1)	N/A	N/A	N/A	N/A	60W A19 (NON-IC ONLY)	60W A19 (NON-IC ONLY)	N/A	N/A
	TL68	WHITE ABALITE FLUSH GLASS SHOWER TRIM	N/A	N/A	N/A	N/A	60W A19 (NON-IC ONLY)	60W A19 (NON-IC ONLY)	N/A	N/A
	TO63WL	WHITE OPEN SHOWER TRIM, WET LISTED	50W PAR30L		N/A	N/A	N/A	N/A	50W PAR30L	
	TO64WL	HIGH WATTAGE WHITE OPEN SHOWER TRIM, WET LISTED	75W PAR38		N/A	N/A	N/A	N/A	75W PAR38	
TO6	WHITE CONE	75W PAR30 65W BR30	150W PAR38 120W BR40 40W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	150W PAR38 120W BR40 100W A19	N/A	N/A	75W PAR30 65W BR30	150W PAR38 120W BR40 40W A19	
TO60B TO60C TO60G	ALZAK REFLECTOR (BLACK TO60B, CLEAR TO60C, GOLD TO60G)	75W PAR30 65W BR30	150W PAR38 120W BR40 40W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	150W PAR38 120W BR40 100W A19	N/A	N/A	75W PAR30 65W BR30	150W PAR38 120W BR40 40W A19	
OPEN	TO61	WHITE OPEN SPLAY	75W PAR30 65W BR30	75W PAR30L 85W BR30 100W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	75W PAR30L 85W BR30 75W A19	N/A	N/A	75W PAR30 65W BR30	75W PAR30L 85W BR30 100W A19
	TO62	WHITE OPEN TRIM	90W PAR38 90W BR40	150W PAR38 120W BR40	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	150W PAR38 120W BR40	N/A	N/A	90W PAR38 90W BR40	150W PAR38 120W BR40
	TO63	WHITE OPEN TRIM	N/A	N/A	N/A	N/A	75W PAR30 65W BR30	75W PAR30 65W BR30	N/A	N/A
	TO83	WHITE OPEN TRIM	50W PAR30	50W PAR30	N/A	50W PAR30	N/A	N/A	50W PAR30	50W PAR30
WALL WASH	TW61BF TB61WBF	BAFFLE WALL WASH (BLACK TW61BF, WHITE TB61WBF)	N/A	60W A19	13,18,26W QUAD TUBE/13,18,26W TRIPLE TUBE	60W A19	N/A	N/A	N/A	60W A19