

Mounting Bases, Cable Ties and Accessories

Select the four-way configuration you need!

Four-Way Adhesive Mounting Base

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction
- For synthetic rubber adhesive (SRA), allow 15-minute setting time for maximum adhesion performance
- For acrylic adhesive, allow 24- to 72-hour setting time for maximum adhesion performance (acrylic-adhesive mounting bases may be re-positioned initially before the adhesive has set)



Four-Way Mini Base



Large Four-Way Base



| STD. PKG. CAT. NO. | BULK PKG. CAT. NO. | MOUNTING METHOD | MAX. TIE WIDTH ACCOM. | LENGTH IN./MM | WIDTH IN./MM | MATERIAL | STD. PKG. QTY. | BULK PKG. QTY. |
|-------------------------------------|--------------------|------------------|-----------------------|---------------|--------------|---------------------------------------|----------------|----------------|
| 4-Way Adhesive Mounting Base | | | | | | | | |
| TC5345A | TC345A | SRA* Adhesive | .19 | 1.13/28.58 | 1.13/28.58 | Nylon 6.6 | 100 | 1,000 |
| — | TC345AFR | SRA* Adhesive | .19 | 1.13/28.58 | 1.13/28.58 | Flame-Retardant Nylon | — | 1,000 |
| TC5345AX | TC345AX | SRA* Adhesive | .19 | 1.13/28.58 | 1.13/28.58 | UV Black | 100 | 1,000 |
| TC5345AHTFR | — | Acrylic Adhesive | .19 | 1.13/28.58 | 1.13/28.58 | Black High-Temp Flame-Retardant Nylon | 100 | 1,000 |
| — | TC345 | TC2PA/Screws | .19 | 1.13/28.58 | 1.13/28.58 | Nylon 6.6 | — | 1,000 |
| 4-Way Mini Base | | | | | | | | |
| TC050X050A-C | TC050X050A | SRA* Adhesive | .10 | .5/12.70 | .5/12.70 | Nylon 6.6 | 100 | 1,000 |
| TC5344A | TC344A | SRA* Adhesive | .14 | .75/19.05 | .75/19.05 | Nylon 6.6 | 100 | 1,000 |
| TC5344AX | TC344AX | SRA* Adhesive | .14 | .75/19.05 | .75/19.05 | UV Black | 100 | 1,000 |
| TC5344 | TC344 | Screw Mount | .14 | .75/19.05 | .75/19.05 | Nylon 6.6 | 100 | 1,000 |
| Large 4-Way Base | | | | | | | | |
| TC150X150A-L | TC150150A | SRA* Adhesive | .19 | 1.5/38.10 | .50/38.10 | Nylon 6.6 | 50 | 500 |
| TC150X150AX-L | TC150X150AX | SRA* Adhesive | .19 | 1.5/38.10 | .50/38.10 | UV Black | 50 | 500 |
| — | TC200X200 | Screw Mount | .30 | 2.0/50.80 | 2.0/50.80 | Nylon 6.6 | 50 | 500 |
| TC200X200A-L | TC200X200A | SRA* Adhesive | .30 | 2.0/50.80 | 2.0/50.80 | Nylon 6.6 | 50 | 500 |
| — | TC368 | Screw Mount | .75 | 2.0/50.80 | 2.0/50.80 | Nylon 6.6 | — | 500 |
| — | TC368A | SRA* Adhesive | .75 | 2.0/50.80 | 2.0/50.80 | Nylon 6.6 | — | 500 |

• Storage/Service Temperature: 32° F to 120° F (0° C to 48° C)

• Application Temperature: 65° F to 100° F (18° C to 37° C)

• Surface Preparation: Surface should be cleaned with alcohol-based (IPA) cleaner before application

*Synthetic Rubber Adhesive

Note: See product expiration date on packages with adhesive. Periodically check product for adhesion and replace as needed. Product is for wire management only and is not intended for use as a primary support of wire, cable, etc.

Two-and Four-Way Adhesive Mounting Base



- 4-way base for cable ties up to .184" maximum width and a two-way base for ties up to .301" maximum width
- May also be mounted with #8 size screw (2 holes)

| STD. PKG. CAT. NO. | BULK PKG. CAT. NO. | MOUNTING METHOD | MAX. TIE WIDTH ACCOM. | LENGTH IN./MM | WIDTH IN./MM | MATERIAL | STD. PKG. QTY. | BULK PKG. QTY. |
|--------------------|--------------------|-----------------|-----------------------|---------------|--------------|-----------------|----------------|----------------|
| TC5347A | TC347A | SRA* Adhesive | .30 | 1.13/28.58 | 1.13/28.58 | Nylon 6.6 | 100 | 1,000 |
| TC5347AX | — | SRA* Adhesive | .30 | 1.13/28.58 | 1.13/28.58 | UV Black | 100 | — |
| — | TC347 | TC2PA/Screws | .30 | 1.13/28.58 | 1.13/28.58 | Nylon 6.6 | — | 1,000 |
| — | TC347FR | TC2PA/Screws | .30 | 1.13/28.58 | 1.13/28.58 | Flame-Retardant | — | 1,000 |
| — | TC347X | TC2PA/Screws | .30 | 1.13/28.58 | 1.13/28.58 | UV Black | — | 1,000 |

Temperature Rating: 32° F to 120° F (0° C to 48° C) *Synthetic Rubber Adhesive

Note: See product expiration date on packages with adhesive. Periodically check product for adhesion and replace as needed. Product is for wire management only and is not intended for use as a primary support of wire, cable, etc.