

Specifications

Photo is representative

Eaton SPD2K0225

Eaton NEMA 1 Surface mount, Accepts PD2, 3-Pole, 225A frame MCCB

General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	SPD2K0225
UPC	786689661854
PRODUCT LENGTH/DEPTH	23.8 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	9 in
PRODUCT WEIGHT	14.3 lb
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Power Defense Enclosure - not approved for Series C/G MCCB



Product specifications

TYPE	CIRCUIT BREAKER ENCLOSURE
AMPERAGE RATING	225 A
ENCLOSURE	NEMA 1
MOUNTING METHOD	Surface mounting
NUMBER OF POLES	Three-pole

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SPD2K0225
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

