

Specifications



Photo is representative

Eaton T20P11S2516

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 220°C, 25 kVA, upright only , Single-phase, 240X480V, 120Y/240 Vac, NEMA ST-20, 1 at +5%, 150°C, 25 kVA, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, DOE 2016

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	T20P11S2516
UPC	786680147623
PRODUCT LENGTH/DEPTH	17 in
PRODUCT HEIGHT	33.5 in
PRODUCT WIDTH	22.5 in
PRODUCT WEIGHT	236 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Physical Attributes

COIL MATERIAL	Aluminum
---------------	----------

Performance Ratings

EFFICIENCY	10 CFR Part 431-2016 (DOE)
------------	----------------------------

ENCLOSURE	NEMA 2
FRAME	FR842A
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated type DS-3 transformer
WIRING CONNECTION	3XA

	2016)
FREQUENCY RATING	60 Hz
KVA RATING	25 kVA
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120Y/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	25 kVA
VOLTAGE RATING	240 X 480 Vac-120Y/240 Vac

Miscellaneous

WEATHERSHIELD	WS45A
----------------------	-------

Resources

BROCHURES

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - T20P11S2516](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton T20P11S2516

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 220°C, 25 kVA, upright only , Single-phase, 240X480V, 120Y/240 Vac, NEMA ST-20, 1 at +5%, 150°C, 25 kVA, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, DOE 2016

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	T20P11S2516
UPC	786680147623
PRODUCT LENGTH/DEPTH	17 in
PRODUCT HEIGHT	33.5 in
PRODUCT WIDTH	22.5 in
PRODUCT WEIGHT	236 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Physical Attributes

COIL MATERIAL	Aluminum
---------------	----------

Performance Ratings

EFFICIENCY	10 CFR Part 431-2016 (DOE)
------------	----------------------------

ENCLOSURE	NEMA 2
FRAME	FR842A
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated type DS-3 transformer
WIRING CONNECTION	3XA

	2016)
FREQUENCY RATING	60 Hz
KVA RATING	25 kVA
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120Y/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	25 kVA
VOLTAGE RATING	240 X 480 Vac-120Y/240 Vac

Miscellaneous

WEATHERSHIELD	WS45A
----------------------	-------

Resources

BROCHURES

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - T20P11S2516](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

