



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T50M 1/2" T FM5 Conduit Body

Crouse-Hinds

| | |
|------------------|--|
| Catalog Number | T50M |
| Manufacturer | Crouse-Hinds |
| Description | Conduit Body, ElectroGalvanized With Aluminum Acrylic Paint, Form 5 Body Type, 1/2 In Trade Size, Threaded Connection, T Shape, Side Cable Entry, 3 Hubs, 1/2 In Hub Size, Tee Side Hub Location, T Configuration, 5.38 In Length, 1.34 In Width, 2.05 In Height, Threaded, 1.06 LB/Ea |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Bodies & Covers |

Features

| | |
|------------|-----------------------------------|
| dimensions | 5.3800 IN X 1.3400 IN X 2.0500 IN |
| Form | Form 5 |

Descriptions

| | |
|------------------------|---|
| Description | 1/2" T FM5 CONDUIT BODY |
| extra long description | CRS-H T50M 1/2 FORM 5 T COND BODY M |
| Features | Form 5 malleable iron conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide access to conductors for maintenance and future system changes. Form 5 conduit bodies are manufactured in trade sizes 1/2" to 4", and are interchangeable with Appleton Form 35 conduit bodies. They are also available with a h |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Eaton |
| GTIN | 00782274756233 |
| UPC | 782274756233 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------------|
| Category Description | FORM 5 CONDULETS, COVERS, & GASKETS |
| Type | Conduit outlet body |

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 1.06 |

Uses, Certifications, and Standards

| | |
|-----------|-------------------------|
| Enclosure | Condulet |
| standard | UL 514B, CSA C22.2, CUL |