




Power up mobile devices quickly, reliably and without the need for bulky AC adapters.

TM826USB

radiant® Tamper-Resistant Duplex Receptacles with USB charging capabilities are designed to upgrade existing receptacles for charging power. This device features an overall 3.1A USB charging capability in two USB charging ports coupled with two AC receptacles, and as part of the radiant® collection, now offers a better fit, form and finish. The external brass back-wire pressure-plate and posted side-wire terminal screws make installation fast and easy.

Features & Benefits

Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.




AC receptacles are tamper-resistant to meet NEC. Patented shutter system — now with black “invisi-shutters” for an invisible effect preferred by end users — helps prevent improper insertion of foreign objects.

TM826USBLA

- Overall 3.1A USB charging capability.
- AC receptacles available in 15A, 125V.

- **Back and side wire termination options** accommodate #14 AWG – #10 AWG stranded and solid copper wire.
- **Multiple color options available.**

3rd Party Compliance

 ETL and cULus Listed

Technical Information

Performance

Electrical

| | |
|------------------------------|--|
| Dielectric Withstand Voltage | Withstands 1500V minimum |
| Maximum Working Voltage | 125V |
| Current Interrupting | Certified for current interrupting at full-rated current (receptacle only) |
| Maximum Temperature Rise | 30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current |

Mechanical


| | |
|------------------------|--|
| Terminal Accommodation | Back and side wire termination options accommodate #14 AWG - #10 AWG stranded and solid copper wire. |
| Product Identification | Ratings are a permanent part of the device |

Environmental

| | |
|-----------------------|---|
| Flammability | UL94 V2 (for device cover) 5V (for device body and frame) |
| Operating Temperature | Maximum continuous +60°C, minimum -40°C without impact |
| RoHS | Compliant |

Materials

| | |
|-----------------|--|
| Face | Polycarbonate |
| Back Body | Nylon |
| Line Contacts | CDA 260 Brass |
| Mounting Strap | .049" Zinc-Plated Steel |
| Terminal Screws | Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate for Color Identification |
| Ground Screw | Tri-Drive Steel with Green Chromate |
| Mounting Screws | Tri-Drive Steel |



TM826USBLA


Warranty

1 Year

Ordering Information

USB Chargers with Duplex Tamper-Resistant Receptacles

| Catalog Number | Rating | | Color | Total Charging Capacity | 3rd Party Compliance | | |
|----------------|--------|-----|--------------|-------------------------|----------------------|-------|-------------------------------|
| | A | V | | | UL498 UL1310 | cULus | C22.2 No. 42 C22.2 No. 223 |
| TM826USBI | 15 | 125 | Ivory | 3.1 Amp | • | • | • |
| TM826USBW | 15 | 125 | White | 3.1 Amp | • | • | • |
| TM826USBBK | 15 | 125 | Black | 3.1 Amp | • | • | • |
| TM826USBLA | 15 | 125 | Light Almond | 3.1 Amp | • | • | • |
| TM826USBNICC6 | 15 | 125 | Nickel | 3.1 Amp | • | • | • |
| TM826USBGCCV4 | 15 | 125 | Graphite | 3.1 Amp | • | • | • |
| TM826USDBCCV4 | 15 | 125 | Dark Bronze | 3.1 Amp | • | • | • |




Vertical Markets

- Residential
- Multiple Dwelling
- Hospitality/Lodging

Also available in the radiant® collection...

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Timers
- Combination Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca






Power up mobile devices quickly, reliably and without the need for bulky AC adapters.

TM826USB

radiant® Tamper-Resistant Duplex Receptacles with USB charging capabilities are designed to upgrade existing receptacles for charging power. This device features an overall 3.1A USB charging capability in two USB charging ports coupled with two AC receptacles, and as part of the radiant® collection, now offers a better fit, form and finish. The external brass back-wire pressure-plate and posted side-wire terminal screws make installation fast and easy.

Features & Benefits

Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.




AC receptacles are tamper-resistant to meet NEC. Patented shutter system — now with black “invisi-shutters” for an invisible effect preferred by end users — helps prevent improper insertion of foreign objects.

TM826USBLA

- Overall 3.1A USB charging capability.
- AC receptacles available in 15A, 125V.

- **Back and side wire termination options** accommodate #14 AWG – #10 AWG stranded and solid copper wire.
- **Multiple color options available.**

3rd Party Compliance

 ETL and cULus Listed

Technical Information

Performance

Electrical

| | |
|------------------------------|--|
| Dielectric Withstand Voltage | Withstands 1500V minimum |
| Maximum Working Voltage | 125V |
| Current Interrupting | Certified for current interrupting at full-rated current (receptacle only) |
| Maximum Temperature Rise | 30°C after 50 cycles at full-rated current after 50 cycles of overload are 150% of rated current with direct current |

Mechanical


| | |
|------------------------|--|
| Terminal Accommodation | Back and side wire termination options accommodate #14 AWG - #10 AWG stranded and solid copper wire. |
| Product Identification | Ratings are a permanent part of the device |

Environmental

| | |
|-----------------------|---|
| Flammability | UL94 V2 (for device cover) 5V (for device body and frame) |
| Operating Temperature | Maximum continuous +60°C, minimum -40°C without impact |
| RoHS | Compliant |

Materials

| | |
|-----------------|--|
| Face | Polycarbonate |
| Back Body | Nylon |
| Line Contacts | CDA 260 Brass |
| Mounting Strap | .049" Zinc-Plated Steel |
| Terminal Screws | Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate for Color Identification |
| Ground Screw | Tri-Drive Steel with Green Chromate |
| Mounting Screws | Tri-Drive Steel |



TM826USBLA


Warranty

1 Year

Ordering Information

USB Chargers with Duplex Tamper-Resistant Receptacles

| Catalog Number | Rating | | Color | Total Charging Capacity | 3rd Party Compliance | | |
|----------------|--------|-----|--------------|-------------------------|----------------------|-------|-------------------------------|
| | A | V | | | UL498 UL1310 | cULus | C22.2 No. 42 C22.2 No. 223 |
| TM826USBI | 15 | 125 | Ivory | 3.1 Amp | • | • | • |
| TM826USBW | 15 | 125 | White | 3.1 Amp | • | • | • |
| TM826USBBK | 15 | 125 | Black | 3.1 Amp | • | • | • |
| TM826USBLA | 15 | 125 | Light Almond | 3.1 Amp | • | • | • |
| TM826USBNICC6 | 15 | 125 | Nickel | 3.1 Amp | • | • | • |
| TM826USBGCCV4 | 15 | 125 | Graphite | 3.1 Amp | • | • | • |
| TM826USDBCCV4 | 15 | 125 | Dark Bronze | 3.1 Amp | • | • | • |




Vertical Markets

- Residential
- Multiple Dwelling
- Hospitality/Lodging

Also available in the radiant® collection...

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Timers
- Combination Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

