



TMCX armored cable glands

Cl. I, Div. 1, Groups A, B, C, D
 Cl. II
 Cl. III
 NEMA 4
 IP56

1G

Cable types:

- Metal clad cable: MC, MC-HL 
- Tray cable: TC 

Features:

- Stainless steel copper-plated spring provides grounding continuity of cable armor (MC cable only)
- Provides explosionproof compound seal on conductors and watertight seal on outer sheath of cable
- Cold Shrink kit is available for extra protection in aggressive environments (see page 232 for more information)
- Supplied with TSC epoxy sealing compound

Standard material:

- Body – aluminum with neoprene seal

Certifications and compliances:



- Class I, Division 1, Groups A, B, C, D
- Class II
- Class III
- UL Listed – UL File No. E122485
- CSA Listed – LR13046
- NEMA 4
- IP56

Operating temperature:


- -25°C to +60°C

Options:

- | Description | Suffix |
|------------------------------|-----------|
| • Brass construction..... | BR |
| • Nickel-plated finish | NP |



1G



NPT thread size	Cat. #	Armor range (H)		Outer sheath (E)		Across flats	Across corners (G)	Length (L)	Thread length (B)
		Min.	Max.	Min.	Max.				
1/2"	TMCX165	0.44	0.65	0.49	0.78	1.25	1.38	2.63	0.75
3/4"	TMCX285	0.60	0.85	0.65	1.00	1.50	1.63	2.88	0.78
1"	TMCX3112	0.80	1.12	0.85	1.31	1.88	2.00	3.13	0.94
1 1/4"	TMCX4140	1.10	1.40	1.15	1.62	2.25	2.44	3.13	0.97
1 1/2"	TMCX5161	1.33	1.61	1.38	1.78	2.50	2.75	3.38	0.97
2"	TMCX6206	1.57	2.06	1.63	2.31	3.25	3.50	5.31	1.00
2 1/2"	TMCX7247	1.93	2.47	1.99	2.72	3.75	4.00	6.06	1.44
3"	TMCX8302	2.45	3.02	2.52	3.28	4.50	4.88	6.06	1.44
3 1/2"	TMCX9352	2.95	3.52	3.02	3.78	5.00	5.38	7.75	1.63
4"	TMCX10402	3.50	4.02	3.58	4.28	5.50	5.88	8.31	1.63



All dimensions in inches.

TMCX armored cable glands

Cl. I, Div. 1, Groups A, B, C, D
 Cl. II
 Cl. III
 NEMA 4
 IP56

1G

Cable types:

- Metal clad cable: MC, MC-HL 
- Tray cable: TC 

Features:

- Stainless steel copper-plated spring provides grounding continuity of cable armor (MC cable only)
- Provides explosionproof compound seal on conductors and watertight seal on outer sheath of cable
- Cold Shrink kit is available for extra protection in aggressive environments (see page 232 for more information)
- Supplied with TSC epoxy sealing compound

Standard material:

- Body – aluminum with neoprene seal

Certifications and compliances:



- Class I, Division 1, Groups A, B, C, D
- Class II
- Class III
- UL Listed – UL File No. E122485
- CSA Listed – LR13046
- NEMA 4
- IP56

Operating temperature:


- -25°C to +60°C

Options:

- | Description | Suffix |
|------------------------------|-----------|
| • Brass construction..... | BR |
| • Nickel-plated finish | NP |



1G



NPT thread size	Cat. #	Armor range (H)		Outer sheath (E)		Across flats	Across corners (G)	Length (L)	Thread length (B)
		Min.	Max.	Min.	Max.				
1/2"	TMCX165	0.44	0.65	0.49	0.78	1.25	1.38	2.63	0.75
3/4"	TMCX285	0.60	0.85	0.65	1.00	1.50	1.63	2.88	0.78
1"	TMCX3112	0.80	1.12	0.85	1.31	1.88	2.00	3.13	0.94
1 1/4"	TMCX4140	1.10	1.40	1.15	1.62	2.25	2.44	3.13	0.97
1 1/2"	TMCX5161	1.33	1.61	1.38	1.78	2.50	2.75	3.38	0.97
2"	TMCX6206	1.57	2.06	1.63	2.31	3.25	3.50	5.31	1.00
2 1/2"	TMCX7247	1.93	2.47	1.99	2.72	3.75	4.00	6.06	1.44
3"	TMCX8302	2.45	3.02	2.52	3.28	4.50	4.88	6.06	1.44
3 1/2"	TMCX9352	2.95	3.52	3.02	3.78	5.00	5.38	7.75	1.63
4"	TMCX10402	3.50	4.02	3.58	4.28	5.50	5.88	8.31	1.63

All dimensions in inches.