ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



# TPC350 3-1/2" Three Piece Coupling

*Appleton/Oz Gedney*

| | |
|---|---|
| Catalog Number | TPC350 |
| Manufacturer | Appleton/Oz Gedney |
| Description | Conduit Hardware, Couplings, Armored Cable, Type: Threaded, Trade Size: 3 1/2 Inch, For Use With: Rigid or Imc, Material: Malleable Iron |
| Weight per unit | 6.2 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

## Features

| | |
|---|---|
| connection | Threaded |
| Connector Type | Threaded Coupling |

## Material, Color, and Finish

| | |
|---|---|
| Color | Metallic |

## Dimensions and Weight

| | |
|---|---|
| Length | 2.54 |

## Descriptions

| | |
|---|---|
| Description | 3-1/2" THREE PIECE COUPLING |
| extra long description | EGS TPC-350 3-1/2 IN 3 PIECE CPLG |
| Long Description | Conduit Hardware, Couplings, Armored Cable, Type: Threaded, Trade Size: 3 1/2 Inch, For Use With: Rigid or IMC, Material: Malleable Iron |
| Product Type | 3-1/2 In 3 Piece CPLG |
| Special Features | 3-1/2 IN Trade Size Three Piece Coupling, For Use With Rigid and IMC Conduit |

## Manufacturer Information

| | |
|---|---|
| Brand | Appleton |
| GTIN | 00687855404759 |
| Manufacturers Part Number | TPC-350 |
| UPC | 687855404759 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type | Three Piece Coupling |

## Trade Size

| | |
|---|---|
| Trade Size | 3.5 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

## Packaging

| | |
|---|---|
| Carton | 5 |
| Weight Per each | 6.2 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Provides threaded coupling between lengths of conduit and IMC elbows, where neither can be rotated |
| standard | NEMA: FB-1;UL Listed: E163167;UL Standard: 514B |