Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY527M 13.5" "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY527M
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie, Natural Color Nylon 6.6, Length Of 343MM (13.5 Inches) For Bundle Diameter Up to 102MM (4.02 Inches), Width Of 6.9MM (0.27 Inch), Tensile Strength Rating Of 534 Newtons (120 Pounds), Operating Temperature Of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), 50 Pack
Weight per unit	0.0140 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	120

Dimensions and Weight

Length	13.5
Thickness	0.06
Width	0.27

Descriptions

Description	13.5" "TY-RAP" CABLE TIE
extra long description	TB TY527M CABLE TIE 120LB 13 IN NAT
Long Description	High Performance Cable Tie, Natural Color Nylon 6.6, Length of 343mm (13.5 Inches) for Bundle Diameter up to 102mm (4.02 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), 50 Pack
Product Type	Cable Tie 120LB 13 In Nat Nyl 2-PC
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210805115
Manufacturers Part Number	TY527M
UPC	786210805115

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty	50

Packaging

Carton	50
Package	500
Weight Per each	0.014

Uses, Certifications, and Standards

standard	UL E49405 / UL E49405