



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UC327 1-1/2 H-Duty GRND Conn

*Nsi Industries*

Catalog Number	UC327
Manufacturer	Nsi Industries
Description	Heavy Duty 3 Cable Parallel Ground Connector For 1 1/2 Inch Pipe 250 MCM-2/0 Awg Made Of High-Copper-Content Alloy For Grounding to 1/2" - 1" Ground Rods and Ground Pipes From 1/4" - 3 1/2" In Parallel or 90 Degree Position. Suitable For Direct Burial In Earth and Concrete. Nuts and Lockwashers Are Silicon Bronze.
Weight per unit	1.9 (lbs/each)
Product Category	Ground Rods & Grounding System

### Material, Color, and Finish

Clamp Material	250 MCM - 2/0 AWG
Insulation Material	Silicon Bronze

### Descriptions

Description	1-1/2 H-DUTY GRND CONN
extra long description	NSI UC-327 U Bolt Clamp 3 Cond. 1 1
Long Description	Heavy Duty 3 Cable Parallel Ground Connector for 1 1/2 Inch Pipe 250 MCM-2/0 AWG Made of high-copper-content alloy for grounding to 1/2" - 1" ground rods and ground pipes from 1/4" - 3 1/2" in parallel or 90 degree position. Suitable for direct burial in earth and concrete. Nuts and lockwashers are silicon bronze.
Product Type	U Bolt Clamp 3 Cond. 1 1/2 Pipe 250-2/0
Special Features	1 1/2 Pipe Size IN

### Manufacturer Information

Brand	98010027731
GTIN	00662381108654
Manufacturers Part Number	UC-327
sub brand	Grounding
UPC	662381108654

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Ground Connector For Three Parrallel Copper Cables

### Packaging

Carton	1
Package	6
Weight Per each	1.85



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

POWER FUSE, CLASS J TYPE; 5-3/4 INCH; UL 248-8, CSA,  
QPL-WF-1814, CE APPROVAL; 600 VAC VOLTAGE RATING; 1-1/2  
INCH DIAMETER; 200000 AMPERE (SYMMETRICAL)  
INTERRUPTING RATING; 200 AMPERE CURRENT RATING; BLADE  
TERMINAL TYPE; FAST ACTING CHARACTERISTICS

standard

UL467