

Eaton TP258

Catalog Number: TP258

Eaton Crouse-Hinds series Octagon Outlet Box, 3-1/4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, Extension ring, 9.0 cubic inch capacity



General specifications

| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series octagon outlet box | TP258 |
| | UPC |
| | 786189102581 |
| Product Length/Depth | Product Height |
| 3.25 in | 1.5 in |
| Product Width | Product Weight |
| 3.25 in | 0.31 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1-1/2"

Capacity

9 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 1/2 in

Material

Steel

Type

Extension ring

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP258](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP258

Catalog Number: TP258

Eaton Crouse-Hinds series Octagon Outlet Box, 3-1/4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, Extension ring, 9.0 cubic inch capacity



General specifications

| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series octagon outlet box | TP258 |
| | UPC |
| | 786189102581 |
| Product Length/Depth | Product Height |
| 3.25 in | 1.5 in |
| Product Width | Product Weight |
| 3.25 in | 0.31 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1-1/2"

Capacity

9 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 1/2 in

Material

Steel

Type

Extension ring

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP258](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)