NEER™ Zinc Offset Nipples and Three Piece Couplings

NEC/CEC:
Listed for Ordinary Locations

NEC:
Listed for Ordinary Locations

RN: 3/4" Offset

Applications

- To provide on offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN–50

Dimensions in Millimeters (Inches)			
Trade Size (Inches)	Body Length	Maximum Diameter	Catalog Number
1/2	62.2 (2.45)	23.9 (0.94)	**RN-50**
3/4	66.0 (2.60)	29.2 (1.15)	**RN-75**
1	70.1 (2.76)	35.6 (1.40)	**RN-100**
1-1/4	73.7 (2.90)	46.7 (1.84)	**RN-125**
1-1/2	77.5 (3.05)	52.3 (2.06)	**RN-150**
2	82.0 (3.23)	67.6 (2.66)	**RN-200**

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish

- Malleable iron/zinc plated


NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC – 50

Illustrated Dimensions



Dimensions in Millimeters (Inches)				
Trade Size (Inches)	A	B	C	Catalog Number
1/2	34.5 (1.36)	33.0 (1.30)	30.5 (1.20)	**TPC-50**
3/4	41.4 (1.63)	39.9 (1.57)	33.0 (1.30)	**TPC-75**
1	43.2 (1.70)	54.1 (2.13)	47.8 (1.88)	**TPC-100**
1-1/4	53.8 (2.12)	62.0 (2.44)	54.4 (2.14)	**TPC-125**
1-1/2	50.8 (2.00)	73.4 (2.89)	66.3 (2.61)	**TPC-150**
2	60.5 (2.38)	86.6 (3.41)	79.5 (3.13)	**TPC-200**
2 - 1/2	64.5 (2.54)	102.4 (4.03)	99.3 (3.91)	**TPC-250**
3	65.0 (2.56)	16.8 (4.60)	110.7 (4.36)	**TPC-300**
3 - 1/2	64.5 (2.54)	17.1 (4.61)	111.0 (4.37)	**TPC-350**
4	100.1 (3.94)	42.5 (5.61)	129.5 (5.10)	**TPC-400**

Visit our website at **www.emerson.com** or contact us at **(800) 621-1506**.
© February 2017

EMERSON

NEER™ Zinc Offset Nipples and Three Piece Couplings

NEC/CEC:
Listed for Ordinary Locations

NEC:
Listed for Ordinary Locations

RN: 3/4" Offset

Applications

- To provide on offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN–50

Dimensions in Millimeters (Inches)			
Trade Size (Inches)	Body Length	Maximum Diameter	Catalog Number
1/2	62.2 (2.45)	23.9 (0.94)	**RN-50**
3/4	66.0 (2.60)	29.2 (1.15)	**RN-75**
1	70.1 (2.76)	35.6 (1.40)	**RN-100**
1-1/4	73.7 (2.90)	46.7 (1.84)	**RN-125**
1-1/2	77.5 (3.05)	52.3 (2.06)	**RN-150**
2	82.0 (3.23)	67.6 (2.66)	**RN-200**

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish

- Malleable iron/zinc plated


NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC – 50

Illustrated Dimensions



Dimensions in Millimeters (Inches)				
Trade Size (Inches)	A	B	C	Catalog Number
1/2	34.5 (1.36)	33.0 (1.30)	30.5 (1.20)	**TPC-50**
3/4	41.4 (1.63)	39.9 (1.57)	33.0 (1.30)	**TPC-75**
1	43.2 (1.70)	54.1 (2.13)	47.8 (1.88)	**TPC-100**
1-1/4	53.8 (2.12)	62.0 (2.44)	54.4 (2.14)	**TPC-125**
1-1/2	50.8 (2.00)	73.4 (2.89)	66.3 (2.61)	**TPC-150**
2	60.5 (2.38)	86.6 (3.41)	79.5 (3.13)	**TPC-200**
2 - 1/2	64.5 (2.54)	102.4 (4.03)	99.3 (3.91)	**TPC-250**
3	65.0 (2.56)	16.8 (4.60)	110.7 (4.36)	**TPC-300**
3 - 1/2	64.5 (2.54)	17.1 (4.61)	111.0 (4.37)	**TPC-350**
4	100.1 (3.94)	42.5 (5.61)	129.5 (5.10)	**TPC-400**

Visit our website at **www.emerson.com** or contact us at **(800) 621-1506**.
© February 2017

EMERSON