

# Specifications

## Eaton TR1107V

Eaton residential grade decorator duplex receptacle,#14-10 AWG,15A,Commercial, Residential,Flush,125V,Side and push,Ivory,Brass,Impact-resistant thermoplastic face,PVC body,5-15R,Duplex,Screw,Thermoplastic,Core pack,Tamper-resistant

### General specifications

<b>PRODUCT NAME</b>	Eaton residential grade decorator duplex receptacle
<b>CATALOG NUMBER</b>	TR1107V
<b>UPC</b>	032664666438
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	3.81 in
<b>PRODUCT WIDTH</b>	0.69 in
<b>PRODUCT WEIGHT</b>	0.01 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Residential grade



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Decorator duplex receptacle
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant
<b>APPLICATION</b>	Commercial/residential
<b>DEVICE GRADE</b>	Standard grade
<b>WIRING METHOD</b>	Side and push
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Decorator
<b>MATERIAL</b>	Thermoplastic
<b>PACKAGING TYPE</b>	Core pack
<b>COLOR</b>	Ivory
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	Push-In Terminals Wiring: #14 AWG copper (CU) Only, Side Wiring: #10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-15R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	Impact-resistant thermoplastic face PVC body
<b>RECEPTACLE TYPE</b>	Duplex

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TR1107V</a> <a href="#">Duplex tamper resistant receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton TR1107V

Eaton residential grade decorator duplex receptacle,#14-10 AWG,15A,Commercial, Residential,Flush,125V,Side and push,Ivory,Brass,Impact-resistant thermoplastic face,PVC body,5-15R,Duplex,Screw,Thermoplastic,Core pack,Tamper-resistant

### General specifications

<b>PRODUCT NAME</b>	Eaton residential grade decorator duplex receptacle
<b>CATALOG NUMBER</b>	TR1107V
<b>UPC</b>	032664666438
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	3.81 in
<b>PRODUCT WIDTH</b>	0.69 in
<b>PRODUCT WEIGHT</b>	0.01 lb
<b>CERTIFICATIONS</b>	cULus Listed NOM
<b>PRODUCT TYPE</b>	Residential grade



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Decorator duplex receptacle
<b>AMPERAGE RATING</b>	15A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Tamper resistant
<b>APPLICATION</b>	Commercial/residential
<b>DEVICE GRADE</b>	Standard grade
<b>WIRING METHOD</b>	Side and push
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Decorator
<b>MATERIAL</b>	Thermoplastic
<b>PACKAGING TYPE</b>	Core pack
<b>COLOR</b>	Ivory
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	Push-In Terminals Wiring: #14 AWG copper (CU) Only, Side Wiring: #10-14 Copper or Copper Clad Aluminum
<b>NEMA CONFIGURATION</b>	5-15R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	Impact-resistant thermoplastic face PVC body
<b>RECEPTACLE TYPE</b>	Duplex

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TR1107V</a> <a href="#">Duplex tamper resistant receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

