legrand®


Pass & Seymour

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

TR5251, TR5351

Rugged construction plus tamper-resistance equals one safe receptacle

Tamper-resistant child safety outlets that conform to 2008 NEC© Article 406.11 are now available as a specification grade single receptacle. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Tri-drive mounting and backed out terminal screws combine to save installation time.



Features & Benefits


Dual mechanical shutter system to help prevent insertion of foreign objects.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

One-piece brass triple-wipe power contacts for lasting retention.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.



TR5351-LA

Field Uses/Vertical Markets

- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

legrand®
Pass & Seymour

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A.	Rating V.	Color	NEMA Config. No.
Single Receptacles Back & Side Wire				
TR5251-I	15	125	Ivory	5-15R
TR5251-W	15	125	White	5-15R
TR5251	15	125	Brown	5-15R
TR5251-LA	15	125	Light Almond	5-15R
TR5351-I	20	125	Ivory	5-20R
TR5351-W	20	125	White	5-20R
TR5351-LA	20	125	Light Almond	5-20R



NEMA 5-15R



NEMA 5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

legrand®
Pass & Seymour


Technical Specifications

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.

Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2



Dimensions for 15 & 20 Amp


Materials

Face	Nylon	Terminal Screws	Tri-Drive Brass
Back Body	PVC	Hex Head Grounding Screw	Tri-Drive Zinc Plated Steel
Contacts	.032 (.8) Brass		
Clamping Plate	.080 Steel	Assembly Rivets	Steel
Mounting Strap	.042 Steel	Mounting Screws	Tri-Drive Steel

Warranty

1 Year

Complementary Devices & Accessories



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF312R1 — Updated March 2008 — For latest specs visit www.legrand.us/passandseymour

© 2011, Legrand/Pass & Seymour EWS/GGXTP

legrand®


Pass & Seymour

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

TR5251, TR5351

Rugged construction plus tamper-resistance equals one safe receptacle

Tamper-resistant child safety outlets that conform to 2008 NEC© Article 406.11 are now available as a specification grade single receptacle. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Tri-drive mounting and backed out terminal screws combine to save installation time.



Features & Benefits


Dual mechanical shutter system to help prevent insertion of foreign objects.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

One-piece brass triple-wipe power contacts for lasting retention.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.



TR5351-LA

Field Uses/Vertical Markets

- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

legrand®
Pass & Seymour

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A.	Rating V.	Color	NEMA Config. No.
Single Receptacles Back & Side Wire				
TR5251-I	15	125	Ivory	5-15R
TR5251-W	15	125	White	5-15R
TR5251	15	125	Brown	5-15R
TR5251-LA	15	125	Light Almond	5-15R
TR5351-I	20	125	Ivory	5-20R
TR5351-W	20	125	White	5-20R
TR5351-LA	20	125	Light Almond	5-20R



NEMA 5-15R



NEMA 5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

Straight Blade Receptacles
Construction Grade Single
Tamper-Resistant 15 & 20A, 125V

legrand®
Pass & Seymour


Technical Specifications

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.

Performance

Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2



Dimensions for 15 & 20 Amp


Materials

Face	Nylon	Terminal Screws	Tri-Drive Brass
Back Body	PVC	Hex Head Grounding Screw	Tri-Drive Zinc Plated Steel
Contacts	.032 (.8) Brass		
Clamping Plate	.080 Steel	Assembly Rivets	Steel
Mounting Strap	.042 Steel	Mounting Screws	Tri-Drive Steel

Warranty

1 Year

Complementary Devices & Accessories



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade



PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF312R1 — Updated March 2008 — For latest specs visit www.legrand.us/passandseymour

© 2011, Legrand/Pass & Seymour EWS/GGXTP