

EMT Couplings, 90° Connectors and Caps/Heads

COMMERCIAL PRODUCTS: EMT FITTINGS

	Catalog Number	Trade Size (Inches)		Dimensions in Inches/Millimeters			Weight Lbs./Kgs. Per 100	
				A	B	C		
Combination Coupling – EMT to Flexible Metal Conduit – Zinc Diecast								
	TW38-50DC †	1/2	—	1.28/ 32.5	1.25/ 31.8	0.94/ 23.9	7.50/ 3.40	
Combination Coupling – EMT to Flexible Metal Conduit – Malleable Body/Nut								
	TWCC38-50 †	1/2	—	0.84/ 21.3	0.63/ 16.0	1.06/ 26.9	12.00/ 5.44	
	TWCC-50	1/2	—	0.88/ 22.4	0.63/ 16.0	1.06/ 26.9	14.50/ 6.58	
	TWCC-75	3/4	—	1.06/ 26.9	0.66/ 16.8	1.31/ 33.3	25.00/ 11.34	
	TWCC-100	1	—	1.19/ 30.2	0.84/ 21.3	1.88/ 47.8	61.00/ 27.67	
Gland Compression 90° Long Connectors – Concrete Tight – Malleable/Steel Nut								
	TWLL-50L	1/2	—	1.88/ 47.8	2.06/ 52.3	0.59/ 15.0	32.00/ 14.51	
	TWLL-75L	3/4	—	2.19/ 55.6	2.44/ 62.0	0.44/ 11.2	50.00/ 22.68	
	TWLL-100L	1	—	2.59/ 65.8	3.00/ 76.2	0.44/ 11.2	105.00/ 47.63	
	TWLL-125L	1-1/4	—	2.81/ 71.4	3.31/ 84.1	0.56/ 14.2	136.00/ 61.69	
Gland Compression 90° Short Connectors – Concrete Tight – Malleable/Steel Nut								
	TWL-50L	1/2	—	1.22/ 31.0	1.31/ 33.3	0.41/ 10.4	20.00/ 9.07	
	TWL-75L	3/4	—	1.31/ 33.3	1.44/ 36.6	0.44/ 11.2	30.00/ 13.61	
	TWL-100L	1	—	1.63/ 41.4	1.56/ 39.6	0.44/ 11.2	53.00/ 24.04	
Set Screw Entrance Caps – Exclusive “Snap-On” Cover – Malleable Iron								
	EF-125	1-1/4	(3) 5/8” and (2) 13/32”	4.31/ 109.5	2.88/ 73.2	3.63/ 92.2	64.00/ 29.03	
	EF-150	1-1/2	(3) 25/32”, (2) 9/16” and (1) 3/8”	5.00/ 127.0	3.31/ 84.1	4.34/ 110.2	93.00/ 42.18	
	EF-200	2	(3) 1”, (2) 3/4 and (3) 17/32”	6.34/ 161.0	4.50/ 114.3	5.56/ 141.2	183.00/ 83.01	
	EF-250	2-1/2	(3) 7/8”, (1) 1” and (3) 1-5/16”	9.00/ 228.6	6.25/ 158.8	7.75/ 196.9	350.00/ 158.76	

† Not UL Listed